

# Toolbox - TOOL-CASE - 1212629


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Tool case, lockable, with adjustable strap, equipped with: cable cutter, diagonal cutter, micro cutter, stripping and sheath removal tools, crimping tool set, combination, needle-nose, and water pump pliers, VDE bladed and Phillips screwdrivers, control cabinet key, voltage tester, ferrule box, blades, tape measure, continuity tester, marking tool, ring and open-end wrench set, adjustable wrench, T-handle Allen key, safety glasses, hammer, 47-piece ratchet socket wrench set, 1/4"

TOOLS FOR YOU

## Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 652483
GTIN	4046356652483

## Technical data

### Dimensions

Length (b)	510 mm
Width (a)	260 mm
Depth	260 mm
Height (c)	270 mm

### General

Note	Tool case
Material	Polyester

### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---------------------------------------------------------------------------------------------------------------

## Articles in set

Cable-cutting tool - CUTFOX 12 - 1212128



Cable cutter, for copper and aluminum up to 12 mm diameter (up to 35 mm<sup>2</sup>)

## Toolbox - TOOL-CASE - 1212629

### Articles in set

Diagonal cutter - CUTFOX-S VDE - 1212207



Diagonal cutter for hard (piano wire) and soft wires, VDE 1000 V AC/1500 V DC tested

---

Diagonal cutter - MICROFOX-SB - 1212489



Electronic diagonal cutter, round head, without chamfer, with opening spring, mirror-polished and oiled, 2-component grip, cutting capacity: soft 0.2 - 2.0 mm; medium hard 1.2 mm; hard 0.5 mm diameter

---

Stripping tool - WIREFOX 10 - 1212150



Stripping tool, for cables and conductors from 0.02 - 10 mm<sup>2</sup>, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm<sup>2</sup> stranded/1.5 mm<sup>2</sup> solid, replaceable stripping blade

---

Stripping tool - WIREFOX-D 13 - 1212162



Stripping tool, for stripping installation lines of Ø 8 - 13 mm, e.g. NYM 3 x 1.5 mm<sup>2</sup> to 5 x 2.5 mm<sup>2</sup>, single line stripping 0.2 mm<sup>2</sup> - 4 mm<sup>2</sup>, with longitudinal cut blade and sliding knife

---

Stripping tool - WIREFOX-D 28 - 1212174



Stripping tool, for stripping lines of Ø 8 - 28 mm

---

## Toolbox - TOOL-CASE - 1212629

### Articles in set

#### Stripping tool - WIREFOX-D 11 - 1212160



Stripping tool, for stripping multicore signal, control and fiberglass wires of  $\varnothing$  2.5 - 11 mm. Insulation thickness up to 1 mm

---

#### Crimping pliers set - CRIMPFOX-M SET - 1212093



Crimping pliers set, consisting of CRIMPFOX-M (pliers) and dies for insulated cable lugs 0.5 ... 2.5 mm<sup>2</sup> (1212074), non-insulated conduit lugs 0.5 ... 6 mm<sup>2</sup> (1212079) and ferrules 0.25 ... 10 mm<sup>2</sup> (1212080) and 16/25 mm<sup>2</sup> (1212081).

---

#### Replacement die - CRIMPFOX-M RCI 6/DIE - 1212073



Die, for Crimpfox-M, for insulated cable lugs 0.1 - 0.4 mm<sup>2</sup> and 4 - 6 mm<sup>2</sup> (light green, yellow), packed in a serial storage box

---

#### Tool - UNIFOX-C VDE - 1212202



Combination pliers, notched gripping surface, VDE 1000 V AC/1500 V DC tested, size: 180 mm

---

#### Tool - UNIFOX-P VDE - 1212204



Needle-nose pliers with blade, notched grip area, VDE 1000 V AC/1500 V DC tested

---

## Toolbox - TOOL-CASE - 1212629

### Articles in set

Tool - UNIFOX-WP - 1212365



Water pump pliers, with groove joint, grip areas with dual notching, acc. to VDE ISO 8976

---

Screwdriver - SZS 0,4X2,5 VDE - 1205037



Screwdriver, slot-headed, VDE insulated, size: 0.4 x 2.5 x 80 mm, 2-component grip, with non-slip grip

---

Screwdriver - SZS 0,5X3,0 VDE - 1207404



Screwdriver, slot-headed, VDE insulated, size: 0.5 x 3.0 x 100 mm, 2-component grip, with non-slip grip

---

Screwdriver - SZS 1,0X4,0 VDE - 1205066



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 4.0 x 100 mm, 2-component grip, with non-slip grip

---

Screwdriver - SZS 1,0X6,5 VDE - 1205079



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 6.5 x 150 mm, 2-component grip, with non-slip grip

---

## Toolbox - TOOL-CASE - 1212629

### Articles in set

Screwdriver - SZK PH0 VDE - 1205147



Screwdriver, PH crosshead, VDE insulated, size: PH 0 x 80 mm, 2-component grip, with non-slip grip

---

Screwdriver - SZK PH1 VDE - 1205150



Screwdriver, PH crosshead, VDE insulated, size: PH 1 x 80 mm, 2-component grip, with non-slip grip

---

Screwdriver - SZK PH2 VDE - 1205163



Screwdriver, PH crosshead, VDE insulated, size: PH 2 x 100 mm, 2-component grip, with non-slip grip

---

Voltage tester - DUSPOL EXPERT - 1209091



Voltage tester, for DC and AC voltages from 12 V to 1000 V AC/1000 V DC, IP65

---

Control cabinet key - USS 4 - 1203149



Control cabinet key, metal, for all common types of control cabinet

---

## Toolbox - TOOL-CASE - 1212629

### Articles in set

#### Range box - AI SORTI BOX RD - 3202960



Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK

---

#### Range box - AI-TWIN SORTI BOX BU - 3202986



Assortment box, supplied with TWIN ferrules according to DIN 46228-4, CSA-certified, box contains 50 pcs. AI-TWIN 2x0,5-8 WH, AI-TWIN 2x0,75-8 GY, AI-TWIN 2x1-8 RD, AI-TWIN 2x1,5-8 BK, 25 pcs. AI-TWIN 2x2,5-10 BU

---

#### Toolbox - TOOL-CASE EMPTY - 1212628



Tool case, unequipped, can be locked, with rubber straps to hold tools in place

---

#### Screwdriver - SF-THEX 2,5-100 - 1212638



T-handle screwdriver, for Allen screws, hexagonal (with chamfer), size: hex 2.5 x 100 mm, ergonomically shaped handle, matt chrome-plated

---

#### Screwdriver - SF-THEX 3-100 - 1212639



T-handle screwdriver, for Allen screws, hexagonal (with chamfer), size: hex 3 x 100 mm, ergonomically shaped handle, matt chrome-plated

# Toolbox - TOOL-CASE - 1212629

## Articles in set

Screwdriver - SF-THEX 4-150 - 1212640



T-handle screwdriver, for Allen screws, hexagonal (with chamfer), size: hex 4 x 150 mm, ergonomically shaped handle, matt chrome-plated

Screwdriver - SF-THEX 5-150 - 1212641



T-handle screwdriver, for Allen screws, hexagonal (with chamfer), size: hex 5 x 150 mm, ergonomically shaped handle, matt chrome-plated

Tool set - SF-SOCKET SET 47 - 1200292



1/4" socket set, 47-piece, 1/4" reversible ratchet, 48 teeth with fast locking system, 50 mm and 100 mm 1/4" extensions, 1/4" screwdriver handle, 150 mm 1/4" flexible extension, 1/4" Cardan joint, 1/4" T-handle  
 2 x 1/4" bit adapter, 13 knurled 1/4" sockets, wrench size: 4 / 4.5 / 5 / 5.5 / 6 / 7 / 8 / 9 / 10 / 11 / 12 / 13 / 14 mm, 21 knurled socket bits: 6 x Torx® T10, T15, T20, T25, T30, T40, 6 x Hex 3, 4, 5, 6, 7, 8 mm, 3 x Phillips recess® PH1, PH2, PH3, 3 x Pozidriv® PZ1, PZ2, PZ3, 3 x slotted 4, 5.5, 7 mm, Allen wrench Hex 1.27, 1.5, 2, 2.5 mm, breakage and impact-resistant plastic case with metal fastening

Measuring instrument - MEASURING TAPE 5M I/M - 1200304



Measuring tape with automatic tape feed and locking mechanism, measuring rail: imperial/metric, length: 5 m

## Classifications

eCl@ss

eCl@ss 10.0.1	21045003
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21043000
eCl@ss 5.1	21049100
eCl@ss 6.0	21049100
eCl@ss 7.0	21045003
eCl@ss 8.0	21045003

## Toolbox - TOOL-CASE - 1212629

### Classifications

#### eCl@ss

eCl@ss 9.0	21045003
------------	----------

#### ETIM

ETIM 3.0	EC000149
ETIM 4.0	EC002498
ETIM 5.0	EC000149
ETIM 6.0	EC000149
ETIM 7.0	EC000149

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	27113201
UNSPSC 18.0	27113201
UNSPSC 19.0	27113201
UNSPSC 20.0	27113201
UNSPSC 21.0	27113201

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212629](#)