

Crimping pliers - CRIMPFOX-CX 10,90-1 - 1212715

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, coaxial connectors, 1.69 mm, 2.54 mm, 5.41 mm, 10.90 mm, four marked die stations, unlockable pressure lock, lateral entry

Your advantages

- Crimping pliers for processing coaxial connectors
- Unlockable pressure lock
- Lateral conductor entry

Key Commercial Data

| | |
|--------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 857642 |
| GTIN | 4046356857642 |

Technical data

Dimensions

| | |
|------------|--------|
| Length (b) | 256 mm |
| Width (a) | 22 mm |
| Height (c) | 80 mm |

General

| | |
|-----------------|-----------------------------|
| Color | black |
| Compression | HEX crimp |
| Type of contact | Coaxial connectors |
| Designation | Crimping position 1 |
| Crimping width | 5.41 mm |
| Designation | Crimping position 2 |
| Crimping width | 10.90 mm |
| Designation | Crimping position 3 |
| Crimping width | 2.54 mm |
| Die station | Crimping position 4 1.69 mm |
| Crimping width | 1.69 mm |
| Weight | 560 g |

Crimping pliers - CRIMPFOX-CX 10,90-1 - 1212715

Technical data

General

| | |
|--------------------|----------------------|
| Min. cross section | 1.69 mm ² |
| Max. cross section | 10 mm ² |

Environmental Product Compliance

| | |
|---------------------------|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |
|---------------------------|---|

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 21043811 |
| eCl@ss 4.0 | 21040300 |
| eCl@ss 4.1 | 21040300 |
| eCl@ss 5.0 | 21040300 |
| eCl@ss 5.1 | 21040300 |
| eCl@ss 6.0 | 21043800 |
| eCl@ss 7.0 | 21043811 |
| eCl@ss 8.0 | 21043811 |
| eCl@ss 9.0 | 21043811 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC001186 |
| ETIM 4.0 | EC000168 |
| ETIM 5.0 | EC000168 |
| ETIM 6.0 | EC000168 |
| ETIM 7.0 | EC000168 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 27112118 |
| UNSPSC 7.0901 | 27111518 |
| UNSPSC 11 | 23171604 |
| UNSPSC 12.01 | 27111518 |
| UNSPSC 13.2 | 27111518 |
| UNSPSC 18.0 | 27111518 |
| UNSPSC 19.0 | 27111518 |
| UNSPSC 20.0 | 27111518 |
| UNSPSC 21.0 | 27111518 |

Approvals

Approvals

Crimping pliers - CRIMPFOX-CX 10,90-1 - 1212715


Approvals

Approvals

EAC

Ex Approvals

Approval details

| | | |
|-----|---|--------------------------|
| EAC |  | RU x- DE.xx08.B.02974 |
|-----|---|--------------------------|

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212715](#)