

Crimping pliers - CRIMPFOX-CATV 8,23-1 - 1212717

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for CATV connectors, 6.65 mm, 8.23 mm, 9.70 mm, three marked die stations, unlockable pressure lock, lateral entry

Your advantages

- Crimping pliers for processing coaxial CATV connectors
- Unlockable pressure lock
- Lateral conductor entry

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 857666
GTIN	4046356857666

Technical data

Dimensions

Length (b)	256 mm
Width (a)	22 mm
Height (c)	80 mm

General

Color	black
Compression	HEX crimp
Type of contact	CATV connector
Designation	Crimping position 1
Crimping width	6.65 mm
Designation	Crimping position 2
Crimping width	8.23 mm
Designation	Crimping position 3
Crimping width	9.70 mm
Weight	560 g
Min. cross section	6.65 mm ²

Crimping pliers - CRIMPFOX-CATV 8,23-1 - 1212717

Technical data

General

Max. cross section	9.7 mm ²
--------------------	---------------------

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC000168
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Approvals

Crimping pliers - CRIMPFOX-CATV 8,23-1 - 1212717

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212717](#)