

Crimping pliers - CRIMPFOX 2,5-M - 1212719

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.25 mm² ... 2.5 mm², lateral entry, trapezoidal crimp

Your advantages

- ✓ All ferrules can be optimally crimped with a minimum amount of effort even in the case of large conductor cross sections
- ✓ Consistently high crimping quality
- ✓ Unlockable pressure lock
- ✓ Marked die stations for precise processing of corresponding cross sections



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 857789
GTIN	4046356857789

Technical data

Dimensions

Length (b)	204 mm
Width (a)	22 mm
Height (c)	76 mm

General

Color	black
Compression	Trapezoidal crimp
Type of contact	Insulated and uninsulated ferrules
Designation	Crimping position 1
Min. cross section	0.5 mm ²
Max. cross section	1.5 mm ²
AWG min	20
AWG max	16
Designation	Crimping position 2
Max. cross section	2.5 mm ²

Crimping pliers - CRIMPFOX 2,5-M - 1212719

Technical data

General

AWG max	14
Designation	Crimping position 3
Max. cross section	0.25 mm ²
AWG max	24
Weight	500 g
Min. cross section	0.25 mm ²
Max. cross section	2.5 mm ²
AWG min	24
AWG max	14

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---------------------------------------------------------------------------------------------------------------

Classifications

eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC000168
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518

Crimping pliers - CRIMPFOX 2,5-M - 1212719

Classifications

UNSPSC

UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	--	--------------------------

Accessories

Accessories

Mounting material

Replacement spring - CRIMPFOX/ SPR-1 - 1212069



Spare recuperating spring

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212719](#)