

## Crimping pliers - CRIMPFOX-RCI DIN 6 - 1212729

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for symmetrical insulated DIN cable lugs, 0.5 mm<sup>2</sup> ... 6.0 mm<sup>2</sup> (red, blue, yellow), three marked die stations, unlockable pressure lock, lateral entry

### Your advantages

- Crimping pliers for cable lugs and connectors
- They unlock as soon as the required crimping pressure is reached, therefore ensuring sufficient pressure is applied.
- The color-coded dies clearly indicate the cross section.
- Unlockable pressure lock



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 857888
GTIN	4046356857888

### Technical data

#### Dimensions

Length (b)	204 mm
Width (a)	22 mm
Height (c)	76 mm

#### General

Color	black
Compression	Oval crimp
Type of contact	Insulated cable lugs
Designation	Crimping position 1
Min. cross section	0.5 mm <sup>2</sup>
Max. cross section	1.5 mm <sup>2</sup>
AWG min	20
AWG max	16
Designation	Crimping position 2
Min. cross section	1.5 mm <sup>2</sup>

# Crimping pliers - CRIMPFOX-RCI DIN 6 - 1212729

## Technical data

### General

Max. cross section	2.5 mm <sup>2</sup>
AWG min	16
AWG max	14
Designation	Crimping position 3
Min. cross section	4 mm <sup>2</sup>
Max. cross section	6 mm <sup>2</sup>
AWG min	12
AWG max	10
Weight	578 g
Min. cross section	0.5 mm <sup>2</sup>
Max. cross section	6 mm <sup>2</sup>
AWG min	20
AWG max	10

### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

## Classifications

### eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

### ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC000168
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604

# Crimping pliers - CRIMPFOX-RCI DIN 6 - 1212729

## Classifications

### UNSPSC

UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		RU x- DE.xx08.B.02974
-----	--	--------------------------

## Accessories

### Accessories

#### Mounting material

Replacement spring - CRIMPFOX/ SPR-1 - 1212069



Spare recuperating spring

---

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212729](#)