

# Diagonal cutter - CUTFOX-SE LM\_DB - 1212839

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Electrician's diagonal cutter, angled shape, with stripping and crimp area, size: 180 mm, packaging type: with bracket for sales display (backcard)

## Your advantages

- ✔ The tools feature ergonomic two-component safety handles
- ✔ Optimum leverage for easy and effortless work
- ✔ Inductively hardened blades for long-term stable cutting performance
- ✔ can strip (1.5 and 2.5 mm<sup>2</sup>), crimp (1.5 - 2.5 mm<sup>2</sup>), cut brass screws, and bend eyes (Ø 4, 5, 6 mm)

## Key Commercial Data

Packing unit	6 pc
GTIN	 4 055626 045597
GTIN	4055626045597

## Technical data

### Dimensions

Length (b)	180 mm
Cable diameter	0.2 mm ... 11 mm

### General

Color	black
Weight	270 g
Min. cross section	0 mm <sup>2</sup>

### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---------------------------------------------------------------------------------------------------------------

## Classifications

### eCl@ss

eCl@ss 10.0.1	21043711
eCl@ss 4.0	21040300

# Diagonal cutter - CUTFOX-SE LM\_DB - 1212839

## Classifications

### eCl@ss

eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043700
eCl@ss 7.0	21043711
eCl@ss 8.0	21043711
eCl@ss 9.0	21043711

### ETIM

ETIM 4.0	EC000165
ETIM 5.0	EC000165
ETIM 6.0	EC000165
ETIM 7.0	EC000165

### UNSPSC

UNSPSC 13.2	27111511
UNSPSC 18.0	27111511
UNSPSC 19.0	27111511
UNSPSC 20.0	27111511
UNSPSC 21.0	27111511

## Approvals

### Approvals

---

### Approvals


EAC

---

### Ex Approvals

---

### Approval details

EAC		RU x- DE.xx08.B.02974
-----	-------------------------------------------------------------------------------------	--------------------------

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212839](#)