

# FO connecting cable - FOC-PN-B-1000/M12-C/SCRJ/1 - 1408865

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled FO cable, round cable, 980/1000 µm POF fiber, M12 fiber optic connector to SC-RJ/IP20

POF cable, assembled with M12 connector to SC-RJ

## Product Description


POF cable, assembled with M12 connector to SC-RJ

## Your advantages

- ✓ 2.2 mm individual wires made from extremely hard-wearing polyamide (PA)
- ✓ Assembled patch cable with test report
- ✓ M12-OPTIC with recessed ferrules to protect against damage
- ✓ optimized polishing for even better attenuation values
- ✓ Rugged polyurethane (PUR) outer sheath
- ✓ Highly tear-resistant aramid strain relief elements
- ✓ Pin connector pattern in accordance with DIN/IEC 61754-27
- ✓ Included in PROFINET planning guideline (v1.14)
- ✓ Robust connector, IP65/IP67
- ✓ Can be used in 10/100 Mbps Ethernet systems
- ✓ Halogen-free, ozone, and UV resistant



## Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 070599
GTIN	4055626070599

## Technical data

### Standards and Regulations

Impact strength	2 Nm / 10 x
Flammability rating according to UL 94	V0


# FO connecting cable - FOC-PN-B-1000/M12-C/SCRJ/1 - 1408865

## Technical data

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Drawings



## Classifications

### eCl@ss

eCl@ss 10.0.1	27061003
eCl@ss 4.0	27061000
eCl@ss 4.1	27061000
eCl@ss 5.0	27061000
eCl@ss 5.1	27061000
eCl@ss 8.0	27061003
eCl@ss 9.0	27061003

### ETIM

ETIM 4.0	EC001263
ETIM 5.0	EC001263
ETIM 6.0	EC001263
ETIM 7.0	EC001263

### UNSPSC

UNSPSC 13.2	26121607
UNSPSC 18.0	26121607
UNSPSC 19.0	26121607
UNSPSC 20.0	26121607
UNSPSC 21.0	26121607

# FO connecting cable - FOC-PN-B-1000/M12-C/SCRJ/1 - 1408865

## Approvals

Approvals

---

Approvals

EAC

---

Ex Approvals

---

## Approval details

EAC		B.01687
-----	--	---------

## Accessories

### Accessories

Circular connectors (device side)

FO transceiver - SACFO-T-MNNA-M16-650-S - 1416716



M12 FO transceiver, duplex, wavelength: 650 nm for 125 Mbps, for POF and PCF fiber, for PCB mounting, M16 fastening thread, with sealing cap, including I<sup>2</sup>C interface for transceiver monitoring and management

### Data plug

Fiber optic coupling - SACFO-J-MNNA-2 - 1416677



Fiber optics coupling M12, duplex, suitable for all fibers, with wall bracket, IP65 degree of protection

Fiber optic contact insert - FOC-M12-RS-POF - 1406421



Replacement ferrule set (10 pcs.) for M12 POF fiber optic connector (Order No. 1416606)

## FO connecting cable - FOC-PN-B-1000/M12-C/SCRJ/1 - 1408865

### Accessories

#### Spare parts

Fiber optic contact insert - FOC-M12-RS-POF - 1406421



Replacement ferrule set (10 pcs.) for M12 POF fiber optic connector (Order No. 1416606)

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1408865](#)