


# FO patch cable - FOC-ST:A-ST:A-GB07/10,0 - 1420807

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Assembled FO cable, break out cable, single mode fiberglass 9/125 µm, connector: B-FOC (ST) / B-FOC (ST), protection type: IP20, for installation in cable ducts or control cabinets, length: 10 m



## Key Commercial Data

Packing unit	1 pc
Minimum order quantity	25 pc
GTIN	 4 055626 242934
GTIN	4055626242934

## Technical data

### Mechanical characteristics

Insertion/withdrawal cycles	≥ 500
Weight	182.7 g

### Ambient conditions

Ambient temperature (operation)	-5 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C

### Line characteristics

Cable type	Single-mode fiberglass
External cable diameter	2.8 mm
Transmission medium	FO
Fiber	Single mode
Cable, attenuation	0.3 dB/km (at 1310 nm), 0.2 dB/km (at 1550 nm)
Attenuation	≤ 0.5 dB

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
------------	--

# FO patch cable - FOC-ST:A-ST:A-GB07/10,0 - 1420807

## Technical data

### Environmental Product Compliance

	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
--	---

## Classifications

### eCl@ss

eCl@ss 10.0.1	27061003
eCl@ss 8.0	27061003
eCl@ss 9.0	27061003

### ETIM

ETIM 5.0	EC001263
ETIM 6.0	EC001263
ETIM 7.0	EC001263

### UNSPSC

UNSPSC 13.2	26121607
UNSPSC 18.0	26121607
UNSPSC 19.0	26121607
UNSPSC 20.0	26121607
UNSPSC 21.0	26121607

## Accessories

### Accessories

#### Data plug

Fiber optic coupling - PSM-SET-BFOC-LINK/2 - 2799429



Coupling; set consisting of 2 couplings for connecting B-FOC plugs

FO accessories - FOC-TOOL-FERRULECLEANER-2.50 - 1407029



2.50 mm ferrule cleaner, for ST, SC, FC, E2000 (also APC), approx. 500 cleaning cycles

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1420807](#)