

# Marshalling panel - CUC-PP-FR19:1U-I-EMPTY:24 BK - 1422979

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Marshalling panel, type: RJ45, degree of protection: IP20, material: PC-GF, connection method: Quick connection, size of housing: 1, color: black



19" patch bay, for 24 inserts

## Your advantages

- assembly without special tools
- integrated cable tray
- Rugged design
- complete grounding concept integrated
- including mounting kit
- Marking window with interchangeable marking strips
- high packing density
- individually customized with RJ45 or FO inserts



## Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4055626319933

## Technical data

### Mechanical characteristics

Connection method	Quick connection
Number of slots	24
No. of cable outlets	24
Weight	810 g
Type	RJ45
Flammability rating according to UL 94	V0

### Ambient conditions

# Marshalling panel - CUC-PP-FR19:1U-I-EMPTY:24 BK - 1422979

## Technical data

### Ambient conditions

Ambient temperature (operation)	5 °C ... 55 °C
Ambient temperature (assembly)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-5 °C ... 55 °C
Degree of protection	IP20

### Material data

Housing material	PC-GF
Width	482.6 mm
Height	43.6 mm
Depth	83.4 mm
Mounting type	19" rack
Assembly instructions	Observe the grounding concept

### Electrical characteristics

Insulation resistance	according to IEC 61010-1
-----------------------	--------------------------

### Standards and Regulations


Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Drawings

Dimensional drawing



19" patch panel

# Marshalling panel - CUC-PP-FR19:1U-I-EMPTY:24 BK - 1422979

## Classifications

### eCl@ss

eCl@ss 10.0.1	27440210
eCl@ss 6.0	27261200
eCl@ss 7.0	27440210
eCl@ss 8.0	27440210
eCl@ss 9.0	27440210

### ETIM

ETIM 6.0	EC002310
ETIM 7.0	EC002310

## Approvals

### Approvals

Approvals

EAC

Ex Approvals

### Approval details

EAC		B.01742
-----	--	---------

## Accessories

### Accessories

#### Data plug

Marshalling panel - CUC-PP-PATCHBAY - 1407994

Marshalling panel, type: 19" rack/fixed housing, degree of protection: IP20, material: Steel, powder-coated, connection method: Screw connection (in connection with the base element), color: light grey RAL 7035



## Marshalling panel - CUC-PP-FR19:1U-I-EMPTY:24 BK - 1422979

### Accessories

Marshalling panel - CUC-PP-PATCHBAY-MH - 1409283

Marshalling panel, type: 19" rack/fix housing, degree of protection: IP20, material: Steel, powder-coated, connection method: Screw connection (in connection with the base element), size of housing: 1, color: light grey RAL 7035



Marshalling panel - CUC-PP-PATCHBAY-MH BK - 1409284

Marshalling distributor panel, 19", 1 HU, with 5 metal brackets, color similar to RAL 9005



### Electronics pliers

Diagonal cutter - MICROFOX-SP-1 - 1212487



Electronic diagonal cutter, tapered head, without chamfer, with opening spring, non-reflective phosphate-treated surface, punched version

### Female insert

RJ45 socket insert - CUC-I-J1ZNI-S/R4IDC8 - 1417274



RJ45 socket insert, type: RJ45, degree of protection: IP20, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>, material: Zinc die-cast, connection method: IDC connection, connection cross section: AWG 26- 22, cable outlet: straight, Adapter-free design

RJ45 coupling - CUC-I-D1ZNI-S/R4GC8 - 1041760



RJ45 coupling, degree of protection: IP20, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>, material: Zinc die-cast, connection method: 2x RJ45, Adapter-free design

## Marshalling panel - CUC-PP-FR19:1U-I-EMPTY:24 BK - 1422979

### Accessories

Fiber optic coupling - FOC-I-D1PGN-S/LCGCSM - 1041780



Fiber optic coupling, type: LC, degree of protection: IP20, material: PBT, connection method: Coupling, cable outlet: straight

---

Fiber optic coupling - FOC-I-D1PGR-S/SCGCSM - 1041800



Fiber optic coupling, type: SC, degree of protection: IP20, material: PBT, connection method: Coupling, cable outlet: straight

---

Fiber optic coupling - FOC-I-D1PGY-S/MPAGC - 1041820



Fiber optic coupling, degree of protection: IP20, connection method: Coupling, cable outlet: straight

---

Fiber optic coupling - FOC-I-D1PGY-S/MPBGC - 1041840



Fiber optic coupling, degree of protection: IP20, connection method: Coupling, cable outlet: straight

---

### Additional products

Screw set - CUC-PP-FRAME-SCREWSET - 1407989



Screw set, fixing material for the frame

---

## Marshalling panel - CUC-PP-FR19:1U-I-EMPTY:24 BK - 1422979

### Accessories

Cable tie - CUC-PP-MODUL-CABLEFIXSET - 1407991



Cable binder, fixing material for module cable routing

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1422979](#)