


Cable - CABLE-D62F/M/45/0.14/S/150/GK2 - 2310837

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Assembled shielded round cable with a 62-pos. HD D-SUB female connector and pin strip, cable length: 1,5 m



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 125307
GTIN	4046356125307

Technical data

General

Nominal voltage U _N	25 V AC
	50 V DC
Max. current carrying capacity per path	1 A
Length of cable	1.5 m
Single wire, cross section	0.14 mm ²
Single wire, cross section [AWG]	26
External diameter	12.2 mm
Shielding	yes
	Tinned copper-braided shield, approx. 85% covering
Outer sheath, material	PVC
External sheath, color	gray

Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-30 °C ... 70 °C

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Approvals

Approvals

Cable - CABLE-D62F/M/45/0.14/S/150/GK2 - 2310837


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.A*30.B00767
-----	---	-------------------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2310837](#)