

# Cable - CABLE-D62SUBH/B/B/ 300/K4G/GK2 - 2311991

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Assembled, shielded round cable, with 62-pos. HD D-SUB female connector at both ends; cable length: 3 m



## Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356332743

## Technical data

### General

Nominal voltage $U_N$	25 V AC
	50 V DC
Max. current carrying capacity per path	1 A
Length of cable	3 m
Single wire, cross section	0.14 mm <sup>2</sup>
Single wire, cross section [AWG]	26
External diameter	12.2 mm
Shielding	yes
	Tinned copper-braided shield, approx. 85% covering
Outer sheath, material	PVC
External sheath, color	gray

### Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-30 °C ... 70 °C

### Connector 1

Connection name	Field level
Connection method	High-density D-SUB socket strip

# Cable - CABLE-D62SUBH/B/B/ 300/K4G/GK2 - 2311991

## Technical data

### Connector 1

Number of connections	1
Number of positions	62

### Connector 2

Connection name	Controller level
Connection method	High-density D-SUB socket strip
Number of connections	1
Number of positions	62

### Supported controller

Controller	Teleperm XP
------------	-------------

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		RU C- DE.A*30.B00767
-----	---	-------------------------

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2311991](#)