

## Crimping pliers - CRIMPFOX-P CC 0.75 L - 1064998

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for COMBICON crimp connectors with cross section: 0.14 ... 0.75 mm<sup>2</sup>. Unlockable pressure lock, precise parallel crimping, front entry, B crimp, incl. 2 positioning aids

### Your advantages

- Precision-manufactured dies ensure consistently high levels of quality during contact processing
- High crimping force with low manual force
- Marked die stations for precise processing of corresponding cross sections
- Parallel motion sequences of the dies for symmetrical and optimum crimping results
- Female crimp contact PTCM-MP-P...
- Female crimp contact MCC 0,5-MP...
- 

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 722979
GTIN	4055626722979

### Technical data

#### Dimensions

Length (b)	233 mm
------------	--------

#### General

Compression	B crimp
Designation	Crimping position 1
Max. cross section	0.34 mm <sup>2</sup>
AWG max	22
Designation	Crimping position 2
Max. cross section	0.5 mm <sup>2</sup>
AWG max	20
Designation	Crimping position 3
Max. cross section	0.75 mm <sup>2</sup>
AWG max	18
Die station	Crimping position 4

# Crimping pliers - CRIMPFOX-P CC 0.75 L - 1064998

## Technical data

### General

Min. cross section	0.14 mm <sup>2</sup>
Max. cross section	0.25 mm <sup>2</sup>
AWG min	26
AWG max	24
Weight	450 g
Min. cross section	0.14 mm <sup>2</sup>
Max. cross section	0.75 mm <sup>2</sup>

## Classifications

### eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 9.0	21043811

### ETIM

ETIM 6.0	EC000168
ETIM 7.0	EC000168

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		RU x- DE.xx08.B.02974
-----	--	--------------------------

## Accessories

Accessories

Crimp contact

## Crimping pliers - CRIMPFOX-P CC 0.75 L - 1064998

### Accessories

Accessories - PTCM-MP-P 0,14-0,5 - 1013781



Crimp contact, type of contact: Female connector, connection method: Crimp connection, contact surface: Tin

---

Accessories - PTCM-MP-P 0,34-0,75 - 1013780



Crimp contact, type of contact: Female connector, connection method: Crimp connection, contact surface: Tin

---

Accessories - PTCM-MP-PI 0,14-0,5 - 1013990



Crimp contact, type of contact: Male connector, connection method: Crimp connection, contact surface: Tin

---

Accessories - PTCM-MP-PI 0,34-0,75 - 1013989



Crimp contact, type of contact: Male connector, connection method: Crimp connection, contact surface: Tin

---

Accessories - MCC 0,5-MP AU 0,14-0,5 - 1013425



Crimp contact, type of contact: Female connector, connection method: Crimp connection, contact surface: Gold,  
Conductor cross section flexible: 0.14 ...0.5 mm<sup>2</sup>

---

## Crimping pliers - CRIMPFOX-P CC 0.75 L - 1064998

### Accessories

Accessories - MCC 0,5-MP AU 0,34-0,75 - 1013419



Crimp contact, type of contact: Female connector, connection method: Crimp connection, contact surface: Gold, Conductor cross section flexible: 0.34 ...0.75 mm<sup>2</sup>

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1064998](#)