


PCB terminal block - SPT 5/ 3-H-7,5 2RZ - 1714496

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

PCB terminal block, pitch: 7.5 mm, number of positions: 3, color: green, Pin layout: Zigzag pinning W, Solder pin [P]: 4.6 mm



Key Commercial Data

| | |
|--------------|---|
| Packing unit | 50 pc |
| GTIN |  4 055626 383385 |
| GTIN | 4055626383385 |

Technical data

Item properties

| | |
|---------------------|------------------|
| Number of positions | 3 |
| Pin layout | Zigzag pinning W |

Material data - housing

| | |
|---------------|--------------|
| Housing color | green (6021) |
|---------------|--------------|

Dimensions for the product

| | |
|-----------------------------|---------|
| Width [w] | 24.3 mm |
| Height [h] | 19 mm |
| Pitch | 7.5 mm |
| Height (without solder pin) | 14.4 mm |
| Solder pin [P] | 4.6 mm |
| Pin spacing | 13.2 mm |

Dimensions for PCB design

| | |
|---------------|---------|
| Hole diameter | 2.1 mm |
| Pin spacing | 13.2 mm |

Packaging information

| | |
|----------------------------|---------------------|
| Type of packaging | packed in cardboard |
| Pieces per package | 50 |
| Denomination packing units | Pcs. |

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

PCB terminal block - SPT 5/ 3-H-7,5 2RZ - 1714496

Technical data

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27440401 |
| eCl@ss 5.1 | 27261100 |
| eCl@ss 6.0 | 27261100 |
| eCl@ss 7.0 | 27440401 |
| eCl@ss 8.0 | 27440401 |
| eCl@ss 9.0 | 27440401 |

ETIM

| | |
|----------|----------|
| ETIM 5.0 | EC002643 |
| ETIM 6.0 | EC002643 |
| ETIM 7.0 | EC002643 |

Approvals

Approvals


Approvals

EAC / cULus Recognized

Ex Approvals

Approval details

| | | |
|-----|---|---------|
| EAC |  | B.01742 |
|-----|---|---------|

| | | | |
|----------------------------|---|---|-----------------|
| cULus Recognized |  | http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm | E60425-20061129 |
| | B | C | |
| Nominal voltage UN | 600 V | 600 V | |
| Nominal current IN | 36 A | 36 A | |
| mm ² /AWG/kcmil | 24-8 | 24-8 | |

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1714496](#)