

# Functional ground contact - UM-PRO PE CONTACT L2 - 2200162

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



PE contact for UM-PRO panel mounting base for connecting the PCB to the DIN rail at level 2


The figure shows the versions for PCB level 1

## Your advantages

- ✓ Tailor-made housing length, can be cut to length with millimeter precision
- ✓ Easy integration of large electronics components, thanks to the open design
- ✓ Heat-resistant UM-PRO made from polyamide with UL approval up to 100°C
- ✓ Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- ✓ High degree of flexibility, thanks to freely positionable covering hoods



## Key Commercial Data

Packing unit	20 pc
GTIN	 4 046356 547253
GTIN	4046356547253

## Technical data

### Product properties

Brief article description	Functional ground contact
Type	UM-PRO PE CONTACT L2
Order No.	2200162
Housing type	Press-drawn section housings
Mounting type	Screw mounting

### Dimensions

Width [ w ]	6 mm
Height [ h ]	20.8 mm
Depth [ d ]	30.6 mm

# Functional ground contact - UM-PRO PE CONTACT L2 - 2200162

## Technical data

### Material specifications

Color (RAL)	silver
-------------	--------

### Material specifications – metals

Contact material	CuSn
------------------	------

### Ambient conditions

Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 105 °C

### PCB specifications

PCB thickness	1.4 mm ... 1.8 mm
---------------	-------------------

### General information

Type of note	Assembly instruction:
Note	Refer to the data sheet for the range in the download area.

### Note on mounting

Tightening torque / rotational speed	Mounting the PCB: 0.5 Nm-0.6 Nm / 500 rpm-1000 rpm
--------------------------------------	--

### Packaging specifications

Pieces per package	20
Denomination packing units	Pcs.
Outer packaging type	Resealable bag

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27400600
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031

# Functional ground contact - UM-PRO PE CONTACT L2 - 2200162

## Classifications

### ETIM

ETIM 4.0	EC000275
ETIM 5.0	EC002779
ETIM 6.0	EC002779
ETIM 7.0	EC002779

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		B.01742
-----	--	---------

## Accessories

### Necessary add-on products

Profile - UM-PRO PROFILE - 2200148



Press-drawn section housings, Basic profile, profile length (configurable): 3 cm ... 100 cm, color: gray (7035), Note: required profile length = PCB length - 16.2 mm

## Functional ground contact - UM-PRO PE CONTACT L2 - 2200162

### Accessories

Side element - UM-PRO 72 COVER-L BK - 2200151



Lateral element (left) with mounting foot for DIN rails for UM-PRO profiles with a PCB width of 72 mm

---

Side element - UM-PRO 72 COVER-R BK - 2200152



Lateral element (right) with mounting foot for DIN rails for profiles for PCB width 72 mm

---

Side element - UM-PRO 108 COVER-L BK - 2200155



Lateral element (left) with mounting foot for DIN rails for UM-PRO profiles with a PCB width of 108 mm

---

Side element - UM-PRO 108 COVER-R BK - 2200156



Lateral element (right) with mounting foot for DIN rails UM-PRO profiles for PCB width of 108 mm

---

Side element - UM-PRO 122 COVER-L BK - 2200158



Lateral element (left) with mounting foot for DIN rails for UM-PRO profiles with a PCB width of 122 mm

---

## Functional ground contact - UM-PRO PE CONTACT L2 - 2200162

### Accessories

Side element - UM-PRO 122 COVER-R BK - 2200159

Lateral element (right) with mounting foot for DIN rails for UM-PRO profiles for PCB the width of 108 mm



---

### Additional products

Functional ground contact - UM-PRO PE CONTACT L1 - 2200161



PE contact for UM-PRO panel mounting base for connecting the PCB to the DIN rail at level 1

---

Functional ground contact - UM-PRO PE CONTACT L3 - 2200163



PE contact for UM-PRO panel mounting base for connecting the PCB to the DIN rail at level 3

---

Locking - UM-PRO PCB S-LOCK BK - 2200168



Locking element for locking the top PCB onto UM-PRO housing close to the edge

---

Mounting material - UM-PRO PCB C-LOCK L1 BK - 2200164



Locking element for locking the PCB onto UM-PRO housing at level 1

# Functional ground contact - UM-PRO PE CONTACT L2 - 2200162

## Accessories

Mounting material - UM-PRO PCB C-LOCK L2 BK - 2200165



Locking element for locking the PCB onto UM-PRO housing at level 2

---

Mounting material - UM-PRO PCB C-LOCK L3 BK - 2200166



Locking element for locking the PCB onto UM-PRO housing at level 3

---

Mounting flange - UM-PRO MOUNT BK - 2200171



Fuse element for mounting UM-PRO panel mounting bases directly onto the mounting plate

---

Foot element - UM-PRO 72 FOOT BK - 2200153



Press-drawn section housings, Base element for the DIN rail, for mounting below UM-PRO PROFILE (width: 72 mm), Foot element, color: black (9005)

---

Foot element - UM-PRO 108 FOOT BK - 2200157



Press-drawn section housings, Base element for the DIN rail, for mounting below UM-PRO PROFILE (width: 108 mm), Foot element, color: black (9005)

---

## Functional ground contact - UM-PRO PE CONTACT L2 - 2200162

### Accessories

#### Foot element - UM-PRO 122 FOOT BK - 2200160

Press-drawn section housings, Base element for the DIN rail, for mounting below UM-PRO PROFILE (width: 122 mm), Foot element, color: black (9005)



---

#### Covering hood - UM-PRO A/U N 73 CM - 2200310

Press-drawn section housings, Cover, width: 73 mm, profile length (configurable): 3 cm ... 100 cm, height: 24 mm, color: transparent, Note: max. length of the cover = PCB length = 19 mm



---

#### Covering hood - UM-PRO A/U 73 CM - 2200311

Press-drawn section housings, Cover, width: 73 mm, profile length (configurable): 3 cm ... 100 cm, height: 63.2 mm, color: transparent, Note: max. length of the cover = PCB length = 19 mm



---

#### Covering hood - UM-PRO A/U 92 CM - 2200312

Press-drawn section housings, Cover, width: 92 mm, profile length (configurable): 3 cm ... 100 cm, height: 34 mm, color: transparent, Note: max. length of the cover = PCB length = 19 mm



---

#### Side element - UM-PRO LID-73N BK - 2200174

Press-drawn section housings, Side element for low U-shaped profile cover, width: 10.35 mm, height: 78.43 mm, color: black (9005)



## Functional ground contact - UM-PRO PE CONTACT L2 - 2200162

### Accessories

Side element - UM-PRO LID-73 BK - 2200173



Press-drawn section housings, Side element for U-shaped profile cover, width: 10.35 mm, height: 78.49 mm, color: black (9005)

---

Side element - UM-PRO LID-92 BK - 2200172



Press-drawn section housings, Side element for U-shaped profile cover, width: 10.35 mm, height: 97.51 mm, color: black (9005)

---

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2200162](#)