

Side element - UM-ALU 4-100,5 COVER PA BK - 2200952

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Press-drawn section housings, Side elements (left and right) incl. snap-on foot and screws for basic profile, width: 105.4 mm, color: black (9005)



Your advantages

- Item is from the UM-ALU product range
- Aluminum press-drawn section
- Available in lengths from 42.5 mm ... 990 mm, can be cut to any length
- Available in overall widths of 75 mm and 105 mm
- Variety of connection technologies
- Can be mounted on the DIN rail
- EMC protection

Key Commercial Data

| | |
|--------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 716543 |
| GTIN | 4046356716543 |

Technical data

Product properties

| | |
|---------------------------|--|
| Brief article description | Side element |
| Type | UM-ALU 4-100,5 COVER PA BK |
| Order No. | 2200952 |
| Housing type | Press-drawn section housings |
| Type | Side elements (left and right) incl. snap-on foot and screws for basic profile |
| Max. IP code to attain | IP40 |
| Mounting type | Screw mounting |

Dimensions

Side element - UM-ALU 4-100,5 COVER PA BK - 2200952

Technical data

Dimensions

| | |
|-------------|----------|
| Width [w] | 105.4 mm |
|-------------|----------|

Material specifications

| | |
|--|--------------|
| Housing material | PA |
| Color (RAL) | black (9005) |
| Flammability rating according to UL 94 | V0 |

Ambient conditions

| | |
|---|--|
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Relative humidity (storage/transport) | 80 % |

Note on mounting

| | |
|--------------------------------------|---|
| Tightening torque / rotational speed | Screw connection with the basic profile: 0.8 Nm-1 Nm / rpm- rpm |
|--------------------------------------|---|

Packaging specifications

| | |
|----------------------------|---------------------|
| Type of packaging | packed in cardboard |
| Pieces per package | 1 |
| Denomination packing units | Pcs. |
| Outer packaging type | Carton |

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27182701 |
| eCl@ss 4.0 | 27180400 |
| eCl@ss 4.1 | 27180400 |
| eCl@ss 5.0 | 27180500 |
| eCl@ss 5.1 | 27180500 |
| eCl@ss 6.0 | 27182000 |
| eCl@ss 7.0 | 27182701 |
| eCl@ss 8.0 | 27182701 |
| eCl@ss 9.0 | 27182701 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC001031 |
| ETIM 4.0 | EC000721 |
| ETIM 5.0 | EC002779 |
| ETIM 6.0 | EC002779 |

Side element - UM-ALU 4-100,5 COVER PA BK - 2200952

Classifications

ETIM

| | |
|----------|----------|
| ETIM 7.0 | EC002779 |
|----------|----------|

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 31261501 |
| UNSPSC 7.0901 | 31261501 |
| UNSPSC 11 | 31261501 |
| UNSPSC 12.01 | 31261501 |
| UNSPSC 13.2 | 31261501 |
| UNSPSC 18.0 | 31261501 |
| UNSPSC 19.0 | 31261501 |
| UNSPSC 20.0 | 31261501 |
| UNSPSC 21.0 | 31261501 |

Accessories

Accessories

Component housing lower part

Profile - UM-ALU 4-100,5 PROFILE 42,5 - 2200935



Press-drawn section housings, Basic profile, profile width (internal): 100.5 mm, length: 42.5 mm, color: aluminum color

Profile - UM-ALU 4-100,5 PROFILE 60 - 2200936



Press-drawn section housings, Basic profile, profile width (internal): 100.5 mm, length: 60 mm, color: aluminum color

Profile - UM-ALU 4-100,5 PROFILE 95 - 2200937



Press-drawn section housings, Basic profile, profile width (internal): 100.5 mm, length: 95 mm, color: aluminum color

Side element - UM-ALU 4-100,5 COVER PA BK - 2200952

Accessories

Profile - UM-ALU 4-100,5 PROFILE 130 - 2200938



Press-drawn section housings, Basic profile, profile width (internal): 100.5 mm, length: 130 mm, color: aluminum color

Profile - UM-ALU 4-100,5 PROFILE 165 - 2200939



Press-drawn section housings, Basic profile, profile width (internal): 100.5 mm, length: 165 mm, color: aluminum color

Profile - UM-ALU 4-100,5 PROFILE 200 - 2200940



Press-drawn section housings, Basic profile, profile width (internal): 100.5 mm, length: 200 mm, color: aluminum color

Profile - UM-ALU 4-100,5 PROFILE 235 - 2200941



Press-drawn section housings, Basic profile, profile width (internal): 100.5 mm, length: 235 mm, color: aluminum color

Profile - UM-ALU 4-100,5 PROFILE 990 - 2200942



Press-drawn section housings, Basic profile, profile width (internal): 100.5 mm, length: 990 mm, color: aluminum color

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2200952](#)