

Program / configuration memory - SD FLASH 2GB LIGHTCONTROL - 2400327

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Program and configuration memory for extending the internal Flash memory, plug-in, 2 GB, with license key and application program for light control.


Similar figure

Your advantages

- Program and configuration memory
- For storing application programs and other files in the file system of the PLC
- License key for the function block libraries



Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 016214
GTIN	4055626016214

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

General

Supply voltage	3.3 V DC
Supply voltage range	2.7 V DC ... 3.6 V DC

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Program / configuration memory - SD FLASH 2GB LIGHTCONTROL - 2400327

Classifications

eCl@ss

eCl@ss 10.0.1	27242212
eCl@ss 4.0	27250200
eCl@ss 4.1	27250200
eCl@ss 5.0	27242200
eCl@ss 5.1	27242200
eCl@ss 6.0	27242200
eCl@ss 7.0	27242212
eCl@ss 8.0	27242212
eCl@ss 9.0	27242212

ETIM

ETIM 2.0	EC000313
ETIM 3.0	EC000192
ETIM 4.0	EC000192
ETIM 5.0	EC000192
ETIM 6.0	EC000192
ETIM 7.0	EC000192

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	32101601
UNSPSC 13.2	32101606
UNSPSC 18.0	32101606
UNSPSC 19.0	32101606
UNSPSC 20.0	32101606
UNSPSC 21.0	32101606

Accessories

Accessories

Controller

Controller - ILC 171 ETH 2TX - 2700975



The Inline controller offers the option of communicating via PROFINET and Modbus/TCP. Programming is carried out using PC Worx Express or PC Worx (IEC 61131-3).

Program / configuration memory - SD FLASH 2GB LIGHTCONTROL - 2400327

Accessories

I/O component

Inline terminal - IB IL 24 DO8/HD-PAC - 2700172



Inline, Digital output terminal, Digital outputs: 8, 24 V DC, 500 mA, connection method: 1-wire, transmission speed in the local bus: 500 kbps, degree of protection: IP20, including Inline connector and labeling field

Inline terminal - IB IL 24 DI8/HD-PAC - 2700173



Inline, Digital input terminal, Digital inputs: 8, 24 V DC, connection method: 1-wire, transmission speed in the local bus: 500 kbps, degree of protection: IP20, including Inline connector and labeling field

Inline terminal - IB IL AI 2/SF-PAC - 2861302



Inline, Analog input terminal, Analog inputs: 2, 0 V ... 10 V, -10 V ... 10 V, 0 mA ... 20 mA, 4 mA ... 20 mA, -20 mA ... 20 mA, connection method: 2-wire, transmission speed in the local bus: 500 kbps, degree of protection: IP20, including Inline connector and labeling field

Inline function terminal - IB IL RS 485/422-PRO-PAC - 2863627



Inline RS-485/422 function terminal, for serial data transmission, complete with accessories (connector and labeling field), 1 serial input and output channel in RS-485/422 design, pure process data communication

Inline function terminal - IB IL PM 3P/N/EF-PAC - 2700965



Inline power measurement terminal for direct measurement of AC currents up to 5 A, including neutral conductor current and phase conductor voltages up to 400 V AC (phase/neutral conductor) or 690 V AC (phase/phase) complete with accessories (connectors and labeling fields)

Program / configuration memory - SD FLASH 2GB LIGHTCONTROL - 2400327

Accessories

Communication module - IB IL DALI/PWR-PAC - 2897813



Inline, DALI master, integrated DALI power supply unit, safe electrical isolation, transmission speed in the local bus: 500 kbps, degree of protection: IP20, including Inline connectors and marking fields

Communication module - IB IL DALI-PAC - 2897910



Inline, DALI master, Extension for IB IL DALI/PWR-PAC, transmission speed in the local bus: 500 kbps, degree of protection: IP20, including Inline connector and labeling field

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2400327](#)