

Router - FL MGuard RS4000 TX/TX-P - 2702259

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Security appliance in metal housing, with ATEX and IECEx approval with extended temperature range, SD card slot, OPC/Modbus inspector, intelligent firewall with full scope of functions for maximum security and ease of configuration, router with NAT/1:1 NAT, from FW 8.5: VPN for up to 250 tunnels, CIFS Integrity Monitoring, redundancy function

The figure shows a version of the product

Product Description

Router with intelligent firewall and OPC/Modbus inspector with ATEX and IECEx approval, from FW 8.5: VPN for up to 250 tunnels, CIFS Integrity Monitoring, redundancy function, metal housing, slot for SD memory card, extended temperature range

Your advantages

- Maximum security
- OPC firewall
- Deep Packet Inspection
- OPC inspector
- Maximum performance
- Central management tool



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4055626064161

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	45 mm
Height	130 mm
Depth	114 mm

Router - FL MGUARD RS4000 TX/TX-P - 2702259

Technical data

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (5 % ... 95%, relative humidity 95%, temporary condensation according to 3K7/IEC EN 60721-3-3 (except for wind-driven precipitation and ice buildup))

Interfaces

Interface	Ethernet
No. of ports	2 (RJ45 ports)
Transmission physics	Ethernet in RJ45 twisted pair
Transmission speed	10/100 Mbps
Transmission length	100 m (per segment)
Signal LEDs	Supply voltage, data transmission, error, link, activity

Function

Basic functions	Router with intelligent firewall and OPC/Modbus inspector with ATEX and IECEx approval, from FW 8.5: VPN for up to 250 tunnels, CIFS Integrity Monitoring, redundancy function, metal housing, slot for SD memory card, extended temperature range, high-performance firewall/VPN: up to 124 Mbps / 40 Mbps
Supported browsers	HTTPS support required
Processor	330 MHz
Status and diagnostic indicators	LEDs:P1, P2, Fault, State, Error, LAN, WAN
Signal contact control voltage	24 V DC (typical)
Signal contact control current	250 mA (short-circuit-proof)

Security functions

Dynamic Host Configuration Protocol (DHCP) support	Server or Relay Agent
Network Time Protocol (NTP) client	Client
Link Layer Discovery Protocol (LLDP)	As per protocol 802.2
Remote Syslog Logging	On external server
Virtual private network (VPN) throughput	max. 40 Mbps (Router mode, VPN bidirectional throughput) max. 27 Mbps (Stealth mode, VPN bidirectional throughput)
Number of VPN tunnels	250 (Firmware 8.5 or later)
Encryption methods	DES, 3DES, AES-128, -192, -256
Internet Protocol Security (IPsec) mode	ESP tunnel / ESP transport
Authentication	X.509v3 certificates with RSA or PSK
Data integrity	MD5, SHA-1, SHA 256, SHA-512
1:1 Network Address Translation (NAT) in the VPN	Supported
Firewall data throughput	max. 124 Mbps (Router mode, default firewall rules, bidirectional throughput) max. 61 Mbps (Stealth mode, default firewall rules, bidirectional throughput)

Router - FL MGUARD RS4000 TX/TX-P - 2702259

Technical data

Security functions

Firewall rules	Configurable stateful inspection firewall with full scope of functions, deep packet inspection for OPC classic
Filtering	MAC and IP addresses, ports, protocols
Protection against	IP spoofing, DoS and Syn Flood Protection
Routing	Standard routing, NAT, 1:1-NAT, port forwarding

Network expansion parameters

Maximum conductor length (twisted pair)	100 m
---	-------

Supply voltage

Supply voltage	24 V DC (redundant)
Residual ripple	3.6 V _{pp} (within the permitted voltage range)
Supply voltage range	11 V DC ... 36 V DC
Typical current consumption	100 mA (at U _S = 24 V DC)
Max. current consumption	0.24 A

General

Mounting type	DIN rail
Type AX	Stand-alone
Net weight	660 g
Housing material	Metal

Conformity with EMC directives

Developed in acc. with standard	IEC 61000-6-2
Test standard	IEC 61000-4-2 (ESD)
Test result	6 kV contact discharge, 8 kV air discharge
Test standard	IEC 61000-4-3 (immunity to radiated interference)
Test result	10 V/m (80 MHz ... 2000 MHz)
Test standard	IEC 61000-4-4 (burst)
Test result	2 kV power line, 1kV data line
Test standard	IEC 61000-4-5 (surge)
Test result	power line: 2 kV (line/earth), 1 kV (line/line), 1kV data line
Test standard	IEC 61000-4-6 (immunity to conducted interference)
Test result	3 V (10 kHz ... 150 kHz), 10 V (150 kHz ... 80 MHz)

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Type of test	Shock in acc. with EN 60068-2-27/IEC 60068-2-27
Test result	Half-sine 30g, 18 ms, 3 axes
Type of test	Vibration resistance in acc. with EN 60068-2-6/IEC 60068-2-6
Test result	5g, 150 Hz
Noise emission	EN 55022 / Class B
Noise immunity	EN 61000-6-2:2005
Conformance	CE-compliant

Router - FL MGUARD RS4000 TX/TX-P - 2702259

Technical data

Standards and Regulations

ATEX	# II 3G Ex nA IIC T4 Gc
IECEX	Ex nA IIC T4 Gc

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	19170405
eCl@ss 5.0	19030100
eCl@ss 5.1	19030100
eCl@ss 6.0	19170100
eCl@ss 7.0	19170103
eCl@ss 8.0	19170103
eCl@ss 9.0	19170103

ETIM

ETIM 5.0	EC001478
ETIM 6.0	EC001478
ETIM 7.0	EC001478

UNSPSC

UNSPSC 13.2	43222609
UNSPSC 18.0	43222609
UNSPSC 19.0	43222609
UNSPSC 20.0	43222609
UNSPSC 21.0	43222609

Approvals

Approvals

Approvals

UL Listed / cUL Listed / EAC / cULus Listed

Ex Approvals

IECEX / ATEX / UL Listed / cUL Listed / cULus Listed

Router - FL MGUARD RS4000 TX/TX-P - 2702259

Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
-----------	--	---	---------------

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
------------	--	---	---------------

EAC			RU*DE*08.B.00731/19
-----	--	--	---------------------

cULus Listed			
--------------	--	--	--

Accessories

Accessories

Configuration memory

Configuration memory - FL MEM PLUG - 2891259



Exchangeable configuration memory of the device settings for simple device exchange and set-up

Data plug

Assembly tool - FL CRIMPTOOL - 2744869



Crimping pliers, for assembling the RJ45 plugs FL PLUG RJ45..., for assembly on site

Device parameterization

Router - FL MGUARD RS4000 TX/TX-P - 2702259

Accessories

Software - FL MGUARD DM UNLIMITED - 2981974



Central device management software for MGUARD devices for any number of devices in the field. For installation on a PC. No additional licenses required. Download trial version for up to 10 devices.

License

License - FL MGUARD LIC LIFETIME FW - 2700184



License for lifetime software update of FL MGUARD field devices.

License - FL MGUARD LIC CIM - 2701083



License for activating CIFS Integrity Monitoring (CIM) on an FL MGUARD

License - FL MGUARD LIC VPN-250 GROUP - 2700192



License for up to 250 additional VPN online connections

License - FL MGUARD LIC VPN-250 - 2700193



License for up to 250 additional VPN online connections

Router - FL MGUARD RS4000 TX/TX-P - 2702259

Accessories

License - FL MGUARD LIC VPN-10 - 2700194



License for up to 10 additional VPN online connections

Patch cable

Patch cable - FL CAT5 PATCH 0,3 - 2832250



Patch cable, CAT5, assembled, 0.3 m

Patch cable - FL CAT5 PATCH 0,5 - 2832263



Patch cable, CAT5, assembled, 0.5 m

Patch cable - FL CAT5 PATCH 1,0 - 2832276



Patch cable, CAT5, assembled, 1 m

Patch cable - FL CAT5 PATCH 1,5 - 2832221



Patch cable, CAT5, assembled, 1.5 m

Router - FL MGUARD RS4000 TX/TX-P - 2702259

Accessories

Patch cable - FL CAT5 PATCH 2,0 - 2832289



Patch cable, CAT5, assembled, 2 m

Patch cable - FL CAT5 PATCH 3,0 - 2832292



Patch cable, CAT5, assembled, 3 m

Patch cable - FL CAT5 PATCH 5,0 - 2832580



Patch cable, CAT5, assembled, 5 m

Patch cable - FL CAT5 PATCH 7,5 - 2832616



Patch cable, CAT5, assembled, 7.5 m

Patch cable - FL CAT5 PATCH 10,0 - 2832629



Patch cable, CAT5, assembled, 10 m

Router - FL MGUARD RS4000 TX/TX-P - 2702259

Accessories

Patch cable - FL CAT6 PATCH 12,5 - 2891369



Patch cable, CAT6, pre-assembled, 12.5 m

Patch cable - FL CAT6 PATCH 15,0 - 2891372



Patch cable, CAT6, pre-assembled, 15.0 m

Patch cable - FL CAT6 PATCH 20,0 - 2891576



Patch cable, CAT6, pre-assembled, 20.0 m

Plug

RJ45 connector - FL PLUG RJ45 GR/2 - 2744856



RJ45 connector, shielded, with bend protection sleeve, 2 pieces, gray for straight cables, for assembly on site. For connections that are not crossed, it is recommended that you use the connector set with gray bend protection sleeve.

RJ45 connector - FL PLUG RJ45 GN/2 - 2744571



RJ45 connector, shielded, with bend protection sleeve, 2 pieces, green for crossed cables, for assembly on site. For connections that are crossed, it is recommended that the connector set with green bend protection sleeves is used.

Protective cap

Router - FL MGUARD RS4000 TX/TX-P - 2702259

Accessories

Dust protection - FL RJ45 PROTECT CAP - 2832991



Dust protection caps for RJ45 socket

Remote control software

License - MGUARD SECURE VPN CLIENT LIC - 2702579



License for mGuard Secure VPN Client v11.x

SFP module

Media module - FL SFP LX - 2891767



Gigabit SFP module for transmission up to 30 km with a wavelength of 1310 nm.

Media module - FL SFP SX - 2891754



Gigabit SFP module for transmission up to 1 km with a wavelength of 850 nm.

Media module - FL SFP LH - 2989912



Gigabit SFP module for transmission up to 80 km with a wavelength of 1,550 nm.

Router - FL MGUARD RS4000 TX/TX-P - 2702259

Accessories

Media module - FL SFP FX - 2891081



The small form-factor plug-in module provides a fiber optic interface with a data transmission speed of 100 Mbps with a wavelength of 1310 nm (long).

Media module - FL SFP FX SM - 2891082



The small form-factor plug-in module provides a fiber optic interface with a data transmission speed of 100 Mbps with a wavelength of 1310 nm (long).

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2702259](#)