

Termination resistor - FL LCX 50-OHM-RSMA - 2702702


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



The termination resistor is screwed onto an unused antenna connection of a WLAN device, e.g., in leaky wave applications. This terminates the connection with the correct impedance and prevents undesirable emission.

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 0 5 5 6 2 6 2 9 9 2 1 1
GTIN	4055626299211

Technical data

Dimensions

Length	17.4 mm
Diameter	8 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

General

Frequency range	0 GHz ... 6 GHz
Impedance	50 Ω
Connection method	RSMA (male)

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Termination resistor - FL LCX 50-OHM-RSMA - 2702702

Classifications

eCl@ss

eCl@ss 10.0.1	19070403
eCl@ss 5.0	19070400
eCl@ss 5.1	19070400
eCl@ss 6.0	19070400
eCl@ss 7.0	19070403
eCl@ss 8.0	19070403
eCl@ss 9.0	19070403

ETIM

ETIM 4.0	EC000448
ETIM 5.0	EC000448
ETIM 6.0	EC000448
ETIM 7.0	EC000448

UNSPSC

UNSPSC 13.2	32121617
UNSPSC 18.0	32121617
UNSPSC 19.0	32121617
UNSPSC 20.0	32121617
UNSPSC 21.0	32121617

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2702702](#)