

## FO converters - IBS OPTOSUB-MA/M/L-LK-OPC - 2740724


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



INTERBUS fiber optic converter for converting the remote OUT interface to fiber optics, correction of the optical transmission capacity, FO output left



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 590543
GTIN	4017918590543

### Technical data

#### Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

#### Dimensions

Width	65 mm
Height	16 mm
Depth	59 mm

#### Ambient conditions

Degree of protection	IP20
----------------------	------

#### General

Net weight	47.44 g
Color	green

#### Interfaces

Interface	Incoming remote bus
Connection method	D-SUB 9 plug
Transmission length	35 m (50 m system without optical path diagnostics)
	50 m (70 m system with optical path diagnostics)

# FO converters - IBS OPTOSUB-MA/M/L-LK-OPC - 2740724

## Technical data

### Optical interface FO

Wavelength	660 nm
Transmission medium	FO
Connection method	F-SMA

### Standards and Regulations

Connection in acc. with standard	CUL
----------------------------------	-----

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 10.0.1	27242208
eCl@ss 4.0	27250200
eCl@ss 4.1	27250200
eCl@ss 5.0	27242700
eCl@ss 5.1	27242700
eCl@ss 6.0	27242200
eCl@ss 7.0	27242208
eCl@ss 8.0	27242208
eCl@ss 9.0	27242208

### ETIM

ETIM 2.0	EC001467
ETIM 3.0	EC001467
ETIM 4.0	EC001467
ETIM 5.0	EC001423
ETIM 6.0	EC001423
ETIM 7.0	EC001423

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	45111807
UNSPSC 11	45111807
UNSPSC 12.01	45111807
UNSPSC 13.2	39122114
UNSPSC 18.0	39122114
UNSPSC 19.0	39122114

# FO converters - IBS OPTOSUB-MA/M/L-LK-OPC - 2740724

## Classifications

### UNSPSC

UNSPSC 20.0	39122114
UNSPSC 21.0	39122114

## Approvals

### Approvals

---

#### Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

---

#### Ex Approvals

---

### Approval details

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 140324
---------------	--	---	---------------

cUL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 140324
----------------	--	---	---------------

EAC		EAC-Zulassung
-----	--	---------------

cULus Recognized	
------------------	--

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2740724](#)