

Cable - CAB-DSUB37F/RA/OE/22/TP/S/ 3M - 2909709

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Assembled shielded round cable; connection 1: Twisted pair (37-position) (The wires are marked and fitted with ferrules); connection 2: D-SUB socket strip (1x 37-position); cable length: 3 m

Your advantages

- Individual wire marking: 1, 2, 3, 4, etc.
- Twisted-pair wires fitted with ferrules
- Screw connection: 2 UNC 4-40 screws
- Open end at one end
- D-SUB socket or pin strip at one end



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 055626 682396
GTIN	4055626682396

Technical data

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. permissible operating voltage	125 V AC
	125 V DC
Max. current carrying capacity per path	1 A
Length of cable	3 m
External cable diameter	12.3 mm
Single wire, cross section	0.36 mm ²
Single wire, cross section [AWG]	22

Cable - CAB-DSUB37F/RA/OE/22/TP/S/ 3M - 2909709

Technical data

General

Shielding	yes
	Overall foil shield

Connection data

Connection name	Field level
Connection method	D-SUB socket strip
Number of connections	1
Number of positions	37

Connection data 2

Connection name	Controller level
Connection method	Twisted pair
Number of positions	37
Note	The wires are marked and fitted with ferrules

Supported controller

Color code

Connector 1 = connector 2 (optional) = wire color	D-SUB37 (1) = black
	D-SUB37 (2) = red
	D-SUB37 (3) = black
	D-SUB37 (4) = white
	D-SUB37 (5) = black
	D-SUB37 (6) = green
	D-SUB37 (7) = black
	D-SUB37 (8) = blue
	D-SUB37 (9) = black
	D-SUB37 (10) = yellow
	D-SUB37 (11) = black
	D-SUB37 (12) = brown
	D-SUB37 (13) = black
	D-SUB37 (14) = orange
	D-SUB37 (15) = red
	D-SUB37 (16) = white
	D-SUB37 (17) = red
	D-SUB37 (18) = green
	D-SUB37 (19) = red
	D-SUB37 (20) = blue
	D-SUB37 (21) = red
	D-SUB37 (22) = yellow
	D-SUB37 (23) = red
	D-SUB37 (24) = brown
	D-SUB37 (25) = red

Cable - CAB-DSUB37F/RA/OE/22/TP/S/ 3M - 2909709

Technical data

Color code

	D-SUB37 (26) = orange
	D-SUB37 (27) = green
	D-SUB37 (28) = white
	D-SUB37 (29) = green
	D-SUB37 (30) = blue
	D-SUB37 (31) = green
	D-SUB37 (32) = yellow
	D-SUB37 (33) = green
	D-SUB37 (34) = brown
	D-SUB37 (35) = green
	D-SUB37 (36) = orange
	D-SUB37 (37) = white

Classifications

eCl@ss

eCl@ss 10.0.1	27242220
eCl@ss 5.0	27242200
eCl@ss 5.1	27242200
eCl@ss 6.0	27249200
eCl@ss 7.0	27249205
eCl@ss 8.0	27249205
eCl@ss 9.0	27242220

ETIM

ETIM 5.0	EC000237
ETIM 6.0	EC000237
ETIM 7.0	EC000237

Accessories

Accessories

Marker carrier cable

Cable marker carrier - KME - 0807083



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable binders, cable diameter: > 5 mm, lettering field size: 20 mm x 8 mm

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2909709](#)