

## Cover profile - CD COVER 40 WH - 3240647


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cover for cable duct, white, width: 40 mm, length: 2000 mm



### Key Commercial Data

|                        |   |
|------------------------|---|
| Packing unit           | 14 pc   |
| Minimum order quantity | 14 pc   |
| GTIN                   | <br>4 046356 629737 |
| GTIN                   | 4046356629737   |

### Technical data

#### Dimensions

|            |         |
|------------|---------|
| Length (b) | 2000 mm |
| Width (a)  | 40 mm   |
| Height (c) | 14.4 mm |

#### Ambient conditions

|                                 |                 |
|---------------------------------|-----------------|
| Ambient temperature (operation) | -5 °C ... 60 °C |
|---------------------------------|-----------------|

#### General

|  |           |
|--|-----------|
| Color                                  | white     |
| Components                             | Lead-free |
| Flammability rating according to UL 94 | V0        |
| Material                               | PVC       |

#### Standards and Regulations

|  |    |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

#### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|------------|---|

# Cover profile - CD COVER 40 WH - 3240647

## Technical data

### Environmental Product Compliance

|  |  |
|--|--|
|  | No hazardous substances above threshold values |
|--|--|

## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27400776 |
| eCl@ss 4.0    | 27140600 |
| eCl@ss 4.1    | 27140600 |
| eCl@ss 5.0    | 27140600 |
| eCl@ss 5.1    | 27140600 |
| eCl@ss 6.0    | 27400700 |
| eCl@ss 7.0    | 27400776 |
| eCl@ss 8.0    | 27400776 |
| eCl@ss 9.0    | 27400776 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000012 |
| ETIM 3.0 | EC000727 |
| ETIM 4.0 | EC000727 |
| ETIM 5.0 | EC000727 |
| ETIM 6.0 | EC000727 |
| ETIM 7.0 | EC000727 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30101815 |
| UNSPSC 7.0901 | 30101815 |
| UNSPSC 11     | 30101815 |
| UNSPSC 12.01  | 30101815 |
| UNSPSC 13.2   | 39131712 |
| UNSPSC 18.0   | 39131712 |
| UNSPSC 19.0   | 39131712 |
| UNSPSC 20.0   | 39131712 |
| UNSPSC 21.0   | 39131712 |

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3240647](#)