


## Protective hose - WP-STEEL ZC 45 - 3240701

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Protective hose in galvanized steel

### Key Commercial Data

Packing unit	10 M
Minimum order quantity	10 M
GTIN	 4 046356 737210
GTIN	4046356737210

### Technical data

#### Dimensions

Inner diameter (f)	40 mm
Outside diameter	45 mm

#### Ambient conditions

Ambient temperature (operation)	-200 °C ... 220 °C
Degree of protection	IP40

#### General

Color	silver
Type	Spirals
Components	halogen-free
Material	Steel, galvanized
Bending radius, static	82 mm
Bending radius, dynamic	205 mm
Tensile strength	500 N

#### Standards and Regulations

Halogen-free	yes
--------------	-----

# Protective hose - WP-STEEL ZC 45 - 3240701

## Classifications

### eCl@ss

eCl@ss 10.0.1	27430301
eCl@ss 4.0	27140900
eCl@ss 4.1	27140900
eCl@ss 5.0	27140900
eCl@ss 5.1	27140900
eCl@ss 6.0	27140900
eCl@ss 7.0	27430301
eCl@ss 8.0	27430301
eCl@ss 9.0	27430301

### ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001179
ETIM 5.0	EC001179
ETIM 6.0	EC001179
ETIM 7.0	EC001179

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	40141734
UNSPSC 18.0	40141734
UNSPSC 19.0	40141734
UNSPSC 20.0	40141734
UNSPSC 21.0	40141734

## Approvals

### Approvals

---

Approvals

VDE Zeichengenehmigung

---

Ex Approvals

---

### Approval details

# Protective hose - WP-STEEL ZC 45 - 3240701

## Approvals

VDE Zeichengenehmigung



<http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx>

## Accessories

### Accessories

#### Corrugated pipe screw connection

##### Screw connection - WP-G BRASS IP40 PG36 - 3241043



Cable gland made from brass with Pg thread, IP40 protection

---

##### Screw connection - WP-G BRASS IP40 M40 - 3241050



Cable gland made from brass with metric thread, IP40 protection

---

##### Screw connection - WP-GT BRASS PG36 - 3241029



Cable gland made from brass with Pg thread, rotatable, IP40 protection

---

##### Screw connection - WP-GT BRASS M40 - 3241036



Cable gland made from brass with metric thread, rotatable, IP40 protection

---

## Mounting material

## Protective hose - WP-STEEL ZC 45 - 3240701

### Accessories

Hose clamp - WP-BASE HF 45 - 3240973



Hose clamps

---

Protective hose fixing bracket - WP-BASE A PG36 - 3241082



Fixing bracket for protective sleeves, fixed with two screws

---

### Protective cap

Cable protection end sleeve - WP-SC BRASS 45 - 3241071



End sleeves as cable protection, made of brass

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3240701](#)