

## Cable tie - WT-E HF 7,8X300 - 3240724


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable binders ideal for permanent fastening to virtually any surface, with fastening lug for screwing or fixing with rivets

RoHS

### Key Commercial Data

|                        |   |
|------------------------|---|
| Packing unit           | 100 pc  |
| Minimum order quantity | 100 pc  |
| GTIN                   | <br>4 046356 704403 |
| GTIN                   | 4046356704403   |

### Technical data

#### Dimensions

|                |                 |
|----------------|-----------------|
| Length (b)     | 300 mm          |
| Width (a)      | 7.8 mm          |
| Hole diameter  | 6.5 mm          |
| Cable diameter | 4 mm ... 7.5 mm |

#### Ambient conditions

|   |   |
|---|---|
| Ambient temperature (operation)                 | -40 °C ... 85 °C  |
| Ambient temperature (assembly)                  | -10 °C ... 60 °C  |
| Optimum ambient temperature (storage/transport) | 23 °C 50 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat. |
| Short-term temperature                          | 110 °C  |

#### General

# Cable tie - WT-E HF 7,8X300 - 3240724

## Technical data

### General

|  |                                |
|--|--------------------------------|
| Color                                  | transparent                    |
| Type                                   | Internal teeth                 |
| Components                             | free from silicone and halogen |
| Flammability rating according to UL 94 | V2                             |
| Material                               | PA 6.6                         |
| Tensile strength                       | 540 N                          |

### Standards and Regulations

|  |    |
|--|----|
| Resistance to UV radiation             | no |
| Flammability rating according to UL 94 | V2 |

### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27140702 |
| eCl@ss 4.0    | 27140700 |
| eCl@ss 4.1    | 27140700 |
| eCl@ss 5.0    | 27140700 |
| eCl@ss 5.1    | 27140700 |
| eCl@ss 6.0    | 27140700 |
| eCl@ss 7.0    | 27140702 |
| eCl@ss 8.0    | 27140702 |
| eCl@ss 9.0    | 27140702 |

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000046 |
| ETIM 4.0 | EC000046 |
| ETIM 5.0 | EC000046 |
| ETIM 6.0 | EC000046 |
| ETIM 7.0 | EC000046 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30212109 |
| UNSPSC 7.0901 | 27121703 |
| UNSPSC 11     | 27121703 |
| UNSPSC 12.01  | 27121703 |
| UNSPSC 13.2   | 27121703 |
| UNSPSC 18.0   | 39121731 |

## Cable tie - WT-E HF 7,8X300 - 3240724

### Classifications

#### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 19.0 | 39121731 |
| UNSPSC 20.0 | 39121731 |
| UNSPSC 21.0 | 39121731 |

### Accessories

#### Accessories

#### Universal tools

Cable tie tool - UNIFOX-CT 4,8 - 1212475



Cable binder pliers, for plastic cable binders with a width of 2.2 - 4.8 mm, for a material thickness of up to 1.6 mm

Cable tie tool - UNIFOX-CT 4,8P - 1212609



Cable binder pliers, for plastic cable binders with a width of 2.2 - 4.8 mm, for a material thickness of up to 1.6 mm

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3240724](#)