

Protective hose - WP-STEEL ZC 27 - 3240866


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Protective hose in galvanized steel



Key Commercial Data

Packing unit	10 M
Minimum order quantity	10 M
GTIN	 4 046356 738606
GTIN	4046356738606

Technical data

Dimensions

Inner diameter (f)	23 mm
Outside diameter	27 mm

Ambient conditions

Ambient temperature (operation)	-200 °C ... 220 °C
Degree of protection	IP40

General

Color	silver
Type	Spirals
Components	halogen-free
Material	Steel, galvanized
Bending radius, static	48 mm
Bending radius, dynamic	120 mm
Tensile strength	500 N

Standards and Regulations

Halogen-free	yes
--------------	-----

Protective hose - WP-STEEL ZC 27 - 3240866

Classifications

eCl@ss

eCl@ss 10.0.1	27430301
eCl@ss 4.0	27140900
eCl@ss 4.1	27140900
eCl@ss 5.0	27140900
eCl@ss 5.1	27140900
eCl@ss 6.0	27140900
eCl@ss 7.0	27430301
eCl@ss 8.0	27430301
eCl@ss 9.0	27430301

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001179
ETIM 5.0	EC001179
ETIM 6.0	EC001179
ETIM 7.0	EC001179

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	40141734
UNSPSC 18.0	40141734
UNSPSC 19.0	40141734
UNSPSC 20.0	40141734
UNSPSC 21.0	40141734

Approvals

Approvals

Approvals

VDE Zeichengenehmigung

Ex Approvals

Approval details

Protective hose - WP-STEEL ZC 27 - 3240866

Approvals

VDE Zeichengenehmigung



<http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx>

Accessories

Accessories

Corrugated pipe screw connection

Screw connection - WP-G BRASS IP40 PG21 - 3241041



Cable gland made from brass with Pg thread, IP40 protection

Screw connection - WP-G BRASS IP40 M25 - 3241048



Cable gland made from brass with metric thread, IP40 protection

Screw connection - WP-GT BRASS PG21 - 3241027



Cable gland made from brass with Pg thread, rotatable, IP40 protection

Screw connection - WP-GT BRASS M25 - 3241034



Cable gland made from brass with metric thread, rotatable, IP40 protection

Mounting material

Protective hose - WP-STEEL ZC 27 - 3240866

Accessories

Hose clamp - WP-BASE HF 29 - 3240971



Hose clamps

Protective hose fixing bracket - WP-BASE A PG21 - 3241080



Fixing bracket for protective sleeves, fixed with two screws

Protective cap

Cable protection end sleeve - WP-SC BRASS 27 - 3241069



End sleeves as cable protection, made of brass

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3240866](#)