

## Screw connection - WP-GA HF IP69K PG21 BK - 3240906


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, Pg thread, IP68/69k protection, angled

RoHS

### Key Commercial Data

Packing unit	25 pc
Minimum order quantity	25 pc
GTIN	 4 046356 710138
GTIN	4046356710138

### Technical data

#### Dimensions

Length (b)	56 mm
Width (a)	37 mm
Height (c)	58 mm
Diameter	34 mm
Outside diameter	28.5 mm
Cable diameter	28.5 mm ... 28.5 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
Degree of protection	IP68/IP69K

#### General

Color	black
Type	Angled
	Outer thread
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	V2
Material	PA

# Screw connection - WP-GA HF IP69K PG21 BK - 3240906

## Technical data

### Standards and Regulations

Halogen-free	yes
Connection in acc. with standard	UL
Flammability rating according to UL 94	V2

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 10.0.1	27144432
eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109
eCl@ss 9.0	27144432

### ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001178
ETIM 5.0	EC001178
ETIM 6.0	EC000441
ETIM 7.0	EC000441

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121311
UNSPSC 18.0	39121311
UNSPSC 19.0	39121311
UNSPSC 20.0	39121311
UNSPSC 21.0	39121311

## Approvals

### Approvals

# Screw connection - WP-GA HF IP69K PG21 BK - 3240906

## Approvals

Approvals

LR / UL Recognized / VDE Zeichengenehmigung

---

Ex Approvals

---

### Approval details

LR		<a href="http://www.lr.org/en">http://www.lr.org/en</a>
----	--	---

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>
---------------	--	---

VDE Zeichengenehmigung		<a href="http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx">http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx</a>
------------------------	--	---

## Accessories

Accessories

Corrugated pipe

Protective hose - WP-PA HF 28,5 BK - 3240684



Polyamide protective hose, inflammability class V0, UV resistant

---

Protective hose - WP-PA HF-HB 28,5 BK - 3240842



Polyamide protective hose, inflammability class HB, UV resistant

---

Mounting material

## Screw connection - WP-GA HF IP69K PG21 BK - 3240906

### Accessories

Protective hose fixing bracket - WP-BASE A PG21 - 3241080



Fixing bracket for protective sleeves, fixed with two screws

---

### Seal

Flat gasket - WP-FS IP68 PG21 - 3241170



Flat gasket, height: 2.5 mm, diameter: 34 mm, color: black

---

Flat gasket - WP-FS HF IP68 PG21 - 3241184



Flat gasket, height: 2.5 mm, diameter: 34 mm, color: green

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3240906](#)