

## Screw connection - WP-GT PP HF PG29 - 3241007


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland made from PP with Pg thread, rotatable, IP54 protection



### Key Commercial Data

Packing unit	2 pc
Minimum order quantity	2 pc
GTIN	 4 046356 711395
GTIN	4046356711395

### Technical data

#### Dimensions

Width (a)	50 mm
Height (c)	59 mm
Wrench size	45 mm
Outside diameter	36 mm
Cable diameter	27 mm ... 27 mm

#### Ambient conditions

Ambient temperature (operation)	-10 °C ... 110 °C
Degree of protection	IP54

#### General

Color	gray
Type	Rotatable
	Outer thread
Components	halogen-free
Flammability rating according to UL 94	HB
Material	PP

# Screw connection - WP-GT PP HF PG29 - 3241007

## Technical data

### Standards and Regulations

Halogen-free	yes
Flammability rating according to UL 94	HB

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 10.0.1	27144432
eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109
eCl@ss 9.0	27144432

### ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001178
ETIM 5.0	EC001178
ETIM 6.0	EC000441
ETIM 7.0	EC000441

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121311
UNSPSC 18.0	39121311
UNSPSC 19.0	39121311
UNSPSC 20.0	39121311
UNSPSC 21.0	39121311

## Approvals

### Approvals

---

## Screw connection - WP-GT PP HF PG29 - 3241007

### Approvals

Approvals

VDE Zeichengenehmigung

---

Ex Approvals

---

### Approval details

VDE Zeichengenehmigung



<http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx>

### Accessories

Accessories

Corrugated pipe

Protective hose - WP-SPIRAL PVC C 36 - 3240854



Protective hose, spring steel wire with PVC coating, highly stranded

---

Protective hose - WP-SPIRAL PU C HF 36 - 3240861



Protective hose, spring steel wire with PU coating, highly stranded

---

Mounting material

Protective hose fixing bracket - WP-BASE A PG29 - 3241081



Fixing bracket for protective sleeves, fixed with two screws

---

Seal

## Screw connection - WP-GT PP HF PG29 - 3241007

### Accessories

Gasket - WP-OR PG29 - 3241199

Gasket, height: 2 mm, diameter: 38 mm, color: black



---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3241007](#)