

## Screw connection - WP-G BRASS IP65 M40 - 3241064


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland made from brass with metric thread, IP65 protection



### Key Commercial Data

Packing unit	2 pc
Minimum order quantity	2 pc
GTIN	 4 046356 712149
GTIN	4046356712149

### Technical data

#### Dimensions

Length (b)	43 mm
Width (a)	57 mm
Height (c)	43 mm
Wrench size	52 mm
Inner diameter (f)	36.5 mm
Outside diameter	45 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
Degree of protection	IP65

#### General

Color	brass
Type	Straight
	Outer thread
Components	halogen-free
Material	Brass

# Screw connection - WP-G BRASS IP65 M40 - 3241064

## Technical data

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

## Classifications

### eCl@ss

eCl@ss 10.0.1	27430310
eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	21132000
eCl@ss 5.1	21132000
eCl@ss 6.0	21132000
eCl@ss 7.0	27439203
eCl@ss 8.0	27439203
eCl@ss 9.0	27430310

### ETIM

ETIM 3.0	EC000519
ETIM 4.0	EC000519
ETIM 5.0	EC001180
ETIM 6.0	EC001180
ETIM 7.0	EC001180

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	40141734
UNSPSC 18.0	40141734
UNSPSC 19.0	40141734
UNSPSC 20.0	40141734
UNSPSC 21.0	40141734

## Approvals

### Approvals

---

Approvals

VDE Zeichengenehmigung

---

## Screw connection - WP-G BRASS IP65 M40 - 3241064

### Approvals

Ex Approvals

---

### Approval details

VDE Zeichengenehmigung



<http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx>

### Accessories

#### Accessories

##### Corrugated pipe

Protective hose - WP-STEEL PVC C 45 - 3240873



Galvanized steel protective hose with PVC coating

---

### Mounting material

Protective hose fixing bracket - WP-BASE A M40 - 3241087



Fixing bracket for protective sleeves, fixed with two screws

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3241064](#)