


# Cable driller - WG-D HF 20,3 - 3241107

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable drillers, for fast and tool-free bundling of conductors and cables, removable and reusable



## Key Commercial Data

Packing unit	1000 pc
Minimum order quantity	1000 pc
GTIN	 4 046356 717366
GTIN	4046356717366

## Technical data

### Dimensions

Length (b)	39.4 mm
Width (a)	20.3 mm
Cable diameter	17.8 mm ... 20.3 mm

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (assembly)	-10 °C ... 60 °C
Optimum ambient temperature (storage/transport)	23 °C 50 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat.

### General

Color	transparent
Type	Notched strip

# Cable driller - WG-D HF 20,3 - 3241107

## Technical data

### General

Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA 6.6
Tensile strength	0 N

### Standards and Regulations

Resistance to UV radiation	no
Flammability rating according to UL 94	V2

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 10.0.1	27140702
eCl@ss 4.0	27140700
eCl@ss 4.1	27140700
eCl@ss 5.0	24210600
eCl@ss 5.1	24210600
eCl@ss 6.0	24210600
eCl@ss 7.0	24210690
eCl@ss 8.0	24210690
eCl@ss 9.0	27140702

### ETIM

ETIM 3.0	EC000046
ETIM 4.0	EC000046
ETIM 5.0	EC000046
ETIM 6.0	EC000046
ETIM 7.0	EC000046

### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703
UNSPSC 18.0	39121731
UNSPSC 19.0	39121731
UNSPSC 20.0	39121731

## Cable driller - WG-D HF 20,3 - 3241107

### Classifications

#### UNSPSC

UNSPSC 21.0	39121731
-------------	----------

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3241107](#)