

Retaining bracket - CDC-PTRV - 3270167

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Retaining bracket, via four PTRV single modules, pitch: 8.3 mm, width: 35.6 mm, height: 71.5 mm, color: gray

Your advantages

- The PTRV retaining bracket enables a cable duct cover to be accommodated directly



Key Commercial Data

Packing unit	10 pc
GTIN	
GTIN	4055626064512

Technical data

General

Color	gray
Material	PA

Dimensions

Width	35.6 mm
Height	71.5 mm
Pitch	8.3 mm

General

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (For a short time, not exceeding 24 h, -60 to +70 °C)
Permissible humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	125 °C

Retaining bracket - CDC-PTRV - 3270167

Technical data

General

Static insulating material application in cold	-60 °C
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Calorimetric heat release NFPA 130 (ASTM E 1354)	27,5 MJ/kg
Smoke gas toxicity NFPA 130 (SMP 800C)	passed
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27141190
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141190
eCl@ss 8.0	27141190
eCl@ss 9.0	27141190

ETIM

ETIM 5.0	EC002848
ETIM 6.0	EC002848
ETIM 7.0	EC002848

UNSPSC

UNSPSC 13.2	39121421
UNSPSC 18.0	39121410
UNSPSC 19.0	39121410
UNSPSC 20.0	39121410
UNSPSC 21.0	39121410

Accessories

Accessories

Retaining bracket - CDC-PTRV - 3270167

Accessories

Cover

Cover profile - CD-HF COVER 25 - 3240369



Cover for cable duct, light gray, halogen-free, width: 25 mm, length: 2000 mm

Cover profile - CD-HF COVER 30 - 3240370



Cover for cable duct, light gray, halogen-free, width: 30 mm, length: 2000 mm

Cover profile - CD-HF COVER 40 - 3240371



Cover for cable duct, light gray, halogen-free, width: 40 mm, length: 2000 mm

Cover profile - CD-HF COVER 60 - 3240372



Cover for cable duct, light gray, halogen-free, width: 60 mm, length: 2000 mm

Cover profile - CD-HF COVER 80 - 3240373



Cover for cable duct, light gray, halogen-free, width: 80 mm, length: 2000 mm

Retaining bracket - CDC-PTRV - 3270167

Accessories

Cover profile - CD-HF COVER 120 - 3240368



Cover for cable duct, light gray, halogen-free, width: 120 mm, length: 2000 mm

Cover profile - CD-HF COVER 25 - 3240369



Cover for cable duct, light gray, halogen-free, width: 25 mm, length: 2000 mm

Cover profile - CD COVER 25 - 3240285



Cover for cable duct, gray, width: 25 mm, length: 2000 mm

Cover profile - CD COVER 30 - 3240295



Cover for cable duct, gray, width: 30 mm, length: 2000 mm

Cover profile - CD COVER 40 - 3240286



Cover for cable duct, gray, width: 40 mm, length: 2000 mm

Retaining bracket - CDC-PTRV - 3270167

Accessories

Cover profile - CD COVER 60 - 3240287



Cover for cable duct, gray, width: 60 mm, length: 2000 mm

Cover profile - CD COVER 80 - 3240288



Cover for cable duct, gray, width: 80 mm, length: 2000 mm

Cover profile - CD COVER 100 - 3240289



Cover for cable duct, gray, width: 100 mm, length: 2000 mm

Cover profile - CD COVER 120 - 3240290



Cover for cable duct, gray, width: 120 mm, length: 2000 mm

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3270167](#)