



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	Cord retention bracket(s) Installation guide Rack Mounting brackets Toolless Mounting Kit
--------------------	--

Physical

Cable length	10 ft (3.05 m)
Color	Black
Depth	1.73 in (4.4 cm)
Height	70.00 in (177.8 cm)
Net Weight	12.02 lb(US) (5.45 kg)
Width	2.20 in (5.6 cm)

Input

Line Rated Current	16 A
Input current limits	20 A
Load Capacity	5700 VA
Input Frequency	47...63 Hz
Plug standard	NEMA L21-20P
Nominal Input Voltage	3 phase

Output

Number of power socket outlets	21 NEMA 5-20R 6 NEMA L6-20R
--------------------------------	--------------------------------

Conformance

Product certifications	CUL Listed Industry Canada UL Listed
Standards	CSA C22.2 No. 60950-1-03 FCC Part 15 class A ICES-003 UL 60950-1

Environmental

Ambient air temperature for operation	23...113 °F (-5...45 °C)
Relative humidity	5...95 %
Operating altitude	0...15000 ft
Ambient air temperature for storage	-13...149 °F (-25...65 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	00731304222347
Package weight(Lbs)	19.53 lb(US) (8.86 kg)

Packing Units

Package 1 Height	84.02 in (213.4 cm)
Package 1 width	5.98 in (15.2 cm)
Package 1 Length	5.00 in (12.7 cm)

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Halogen content performance	Halogen free product
Optimized Energy Efficiency	Energy efficient product

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP7893](#)