



### Overview

Lead time	Usually in Stock
-----------	------------------

### General

Provided equipment	Installation guide Reusable packaging
--------------------	--

### Physical

Color	Green Gray
Depth	6.00 in (15.23 cm)
Height	1.64 in (4.16 cm)
Net Weight	1.28 lb(US) (0.58 kg)
Maximum Width	3.05 in (7.74 cm)

### Environmental

Ambient air temperature for operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative humidity	0...85 %
Ambient air temperature for storage	-4...140 °F (-20...60 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)

### Batteries & Runtime

Battery Placement	Internal Battery
Battery Slots Empty	0
Included Battery Modules	0
Battery type	Li-Ion (Lithium Ion)
RBC Quantity	1

### Ordering and shipping details

Package weight(Lbs)	1.65 lb(US) (0.75 kg)
---------------------	-----------------------

### Packing Units

Package 1 Height	3.07 in (7.8 cm)
Package 1 width	5.12 in (13 cm)
Package 1 Length	8.15 in (20.7 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[APCRBC146-LI](#)