

Product data sheet

Characteristics

GS2AHT140

External rotary handle, TeSys GS, red handle, front mounting, 3 positions Test-I-O, NEMA 3R, for GS 30-400A UL



Main

Range of Product	TeSys
Range	TeSys
Device short name	GS2AHT
Product or Component Type	Rotary handle
Range compatibility	TeSys GS GS2EU TeSys GS GS2GU TeSys GS GS2JU TeSys GS GS2MU TeSys GS GS2QU
Type of operating handle	External frontal
Handle colour	Red
Handle front plate colour	Yellow

Complementary

Handle positions	Test-O-I
Rotary handle padlocking	With
Switch rated current	30 A 60 A 100 A 200 A 400 A
Standards	UL CSA
Net Weight	0.53 lb(US) (0.24 kg)

Environment

NEMA Degree of Protection	NEMA 3R/12
---------------------------	------------

Ordering and shipping details

Category	22640-IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	3389119411943
Nbr. of units in pkg.	1
Package weight(Lbs)	8.47 oz (240.0 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.76 in (7.0 cm)
Package 1 width	3.54 in (9.0 cm)
Package 1 Length	7.09 in (18.0 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GS2AHT140](#)