



Main

Range	TeSys
Device short name	MN
Product or component type	Voltage release
Device application	Control
Range compatibility	TeSys GV4 TeSys BV4
Voltage release type	Undervoltage release
[Uc] control circuit voltage	380...415 V AC 50 Hz

Complementary

[Ui] rated insulation voltage	415 V conforming to IEC 60947-1
Threshold tripping voltage	< 0.35 Un failsafe opening 0.35...0.7 Un possible opening 0.85...1.1 Un enabled closing
Mounting mode	Internal mounting
Maximum inrush power in VA	7 VA
Maximum hold-in power consumption in VA	7 VA
Mechanical durability	20000 Cycles
Operating time	< 50 ms
Connections - terminals	Spring terminals 1 0.5...1.5 mm ² - cable stiffness: flexible without cable end
Wire stripping length	8 Mm

Environment

Quantity per set	Set of 1
------------------	----------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	64 G
Package 1 Height	3.5 Cm
Package 1 width	6.3 Cm
Package 1 Length	8.4 Cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	640 G

Package 2 Height	13 Cm
Package 2 width	9 Cm
Package 2 Length	19 Cm
Unit Type of Package 3	S03
Number of Units in Package 3	40
Package 3 Weight	3.15 Kg
Package 3 Height	30 Cm
Package 3 width	30 Cm
Package 3 Length	40 Cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: DIN-P, which is known to the State of California to cause cancer, and DID-P, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Product Life Status : **Commercialised**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GV4AU415](#)