



Main

Range	TeSys TeSys Deca
Device short name	GVAU
Product or Component Type	Undervoltage release

Complementary

Range compatibility	GV2ME GV2LE GV2L GV2P GV3L GV3P TeSys Deca
[Uc] control circuit voltage	200 V AC 50 Hz 200...220 V AC 60 Hz
Control circuit voltage limits	0.85...1.1 Un
[Ui] rated insulation voltage	690 V AC IEC 60947-1 600 V AC UL 60947-4-1 600 V AC CSA C22.2 No 60947-4-1
Threshold tripping voltage	0.7...0.35 Un
Inrush power in VA	12 VA AC
Inrush power in W	8 W
Hold-in Power Consumption in VA	3.5 VA AC
Hold-in power consumption in W	1.1 W
Operating time	10...15 ms IEC 60947-1
On-load factor	100 %
Connections - terminals	Screw clamp terminals 1 0.00...0.00 in ² (1...2.5 mm ²)solid Screw clamp terminals 2 0.00...0.00 in ² (1...2.5 mm ²)solid Screw clamp terminals 1 0.00...0.00 in ² (0.75...2.5 mm ²)flexible without cable end Screw clamp terminals 2 0.00...0.00 in ² (0.75...2.5 mm ²)flexible without cable end Screw clamp terminals 1 0.00...0.00 in ² (0.75...1.5 mm ²)flexible with cable end Screw clamp terminals 2 0.00...0.00 in ² (0.75...1.5 mm ²)flexible with cable end
Tightening torque	< 1.4 N.m screw clamp terminals
Mechanical durability	10000 Cycles with GV3P and GV3L 30000 cycles with GV2ME and GV2P
Quantity per Set	Set of 10
Height	3.50 in (89 mm)
Width	0.71 in (18 mm)
Depth	2.60 in (66 mm)
Net Weight	0.23 lb(US) (0.105 kg)
Color	Dark grey

Ordering and shipping details

Category	22367-MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	3389110345988
Nbr. of units in pkg.	1
Package weight(Lbs)	4.09 oz (116.0 g)
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.27 in (8.3 cm)
Package 1 width	1.42 in (3.6 cm)
Package 1 Length	3.58 in (9.1 cm)


Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

GVAU...



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GVAU207](#)