



Main

Range of Product	Harmony iPC
Product or Component Type	Serial line interface
Accessory / separate part category	Connection accessory

Complementary

Accessory / separate part destination	Harmony iPC
Integrated connection type	Mini PCIe full-size 1 SUB-D 32 RS232 50 bit/s...230.4 kbit/s 6.56 ft (2 m)
Input current	500 mA 3.3 V DC
Range Compatibility	Harmony iPC
Width	2.99 in (76 mm)
Height	3.19 in (81 mm)
Depth	1.50 in (38.2 mm)

Environment

Ambient air temperature for operation	-4...140 °F (-20...60 °C)
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Relative Humidity	5...95 % non-condensing

Ordering and shipping details

Category	22574-MAGELIS BOX PC AND PANEL PC
Discount Schedule	MC2
GTIN	3606480795633
Nbr. of units in pkg.	1
Package weight(Lbs)	1.41 oz (40.0 g)
Returnability	No
Country of origin	TW

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.17 in (5.5 cm)
Package 1 width	6.30 in (16 cm)
Package 1 Length	9.29 in (23.6 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	4
Package 2 Weight	3.85 lb(US) (1.748 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[HMIYMINSL42321](#)