

# Product data sheet

## Characteristics

# RM79696044

temperature probe - 1000 mm - for limited space installation

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

|                                       |  |
|---------------------------------------|--|
| Accessory / separate part designation | Probe for limited space installation                         |
| Accessory / separate part destination | Drinks vending machine<br>Control relay<br>Measurement relay |
| Accessory / separate part category    | Relay accessories  |
| Accessory / separate part type        | Probe  |
| Product compatibility                 | RM35LM33MW<br>RM4L   |
| Maximum pressure                      | <= 2 kg/cm <sup>2</sup>                                      |

### Complementary

|                |                           |
|----------------|---------------------------|
| Length         | 39.37 in (1000 mm)        |
| Material       | Stainless steel electrode |
| Product weight | 1.76 lb(US) (0.8 kg)      |

### Environment

|                                       |                |
|---------------------------------------|----------------|
| Ambient air temperature for operation | 176 °F (80 °C) |
|---------------------------------------|----------------|

### Ordering and shipping details

|                       |  |
|-----------------------|--|
| Category              | 22380 - RELAYS-MEASUREMENT (RM17-RM35) |
| Discount Schedule     | CP2                                    |
| GTIN                  | 003389110281767                        |
| Nbr. of units in pkg. | 1                                      |
| Package weight(Lbs)   | 1.76                                   |
| Returnability         | N                                      |
| Country of origin     | FR                                     |

### Offer Sustainability

|                           |  |
|---------------------------|--|
| California proposition 65 | WARNING: This product can expose you to chemicals including:   |
| ----- Substance 1         | Nickel compounds, which is known to the State of California to cause cancer, and   |
| ----- Substance 2         | Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. |
| ----- More information    | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                              |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RM79696044](#)