

Product data sheet

Specifications

APC 24 Port 10/100 Ethernet Switch

AP9224110



Overview

Lead time Usually in Stock

Main

Main Input Voltage 100 V
120 V
200 V
208 V
230 V

Plug standard IEC 60320 C14

Number of rack unit 1U

Number of cables 1

General

Provided equipment User manual
Rack mounting brackets

Physical

Colour Black

Depth 13.2 cm

Height 3.7 cm

Net weight 1.18 kg

Width 25 cm

Conformance

Product certifications cUL listed
CE
TÜV
UL listed

Standards EN 60950
FCC part 15 class A

Environmental

Ambient air temperature for operation 0...45 °C

Relative humidity 10...90 %

Ambient air temperature for storage	-15...65 °C
-------------------------------------	-------------

Storage Relative Humidity	10...90 %
---------------------------	-----------

Packing Units

Package 1 Weight	2 kg
------------------	------

Package 1 Height	10.2 cm
------------------	---------

Package 1 width	52.1 cm
-----------------	---------

Package 1 Length	21.3 cm
------------------	---------

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
-------------------	--

Mercury free	Yes
--------------	-----

RoHS exemption information	Yes
----------------------------	---------------------

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
------	---

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP9224110](#)