

Product data sheet

Specifications



Roof Fan Tray 230V 60HZ for NetShelter WX Enclosures

AR8207BLK



Overview

Presentation	The Rack Fan Tray is a low cost solution that aids in heat removal from a Netshelter Enclosure. The system easily installs into the top of the enclosure and expels heat from the roof of the rack. Wall-mounted enclosures have the additional option of installing the rack fan tray systems in the base of the rack as well. The fan trays are designed to promote bottom to top airflow within the enclosure.
Lead time	Usually in Stock

Main

Main Input Voltage	208 V 230 V
Plug standard	IEC 60320 C14 Schuko CEE 7/7P BS1363A British
Number of cables	3

General

Provided equipment	Installation guide 1 x IEC to IEC 320 power cord
---------------------------	---

Physical

Color	Black
Depth	6.89 in (17.5 cm)
Height	2.13 in (5.4 cm)
Net Weight	4.01 lb(US) (1.82 kg)
Width	12.52 in (31.8 cm)

Input

Input Frequency	50/60 Hz
------------------------	----------

Conformance

Product Certifications	CSA UL Listed
-------------------------------	------------------

Ordering and shipping details

GTIN	00731304120216
Package weight(Lbs)	6.02 lb(US) (2.73 kg)

Packing Units

Package 1 Height	2.28 in (5.8 cm)
Package 1 width	12.60 in (32 cm)
Package 1 Length	9.21 in (23.4 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AR8207BLK](#)