

Product data sheet

Specifications



EcoStruxure Machine SCADA Expert Thin Client License

HMIVXLTC

! To be discontinued on: 31 March 2022

! To be end-of-service on: 01 April 2022

! To be discontinued

Product availability : Non-Stock - Not normally stocked in distribution facility

Price* : 500.00 USD

Main

Range of Product	EcoStruxure Machine SCADA Expert
Product or Component Type	Software
User Language	Multi-language
Format	Sticker
Previous software version	V8.1 SP5

Complementary

Range Compatibility	Harmony GTU Harmony iPC
Software Designation	Thin client
Type of License	Single (1 station)
Software Type	EcoStruxure machine SCADA Expert software
System requirements	> 2 GB HDD storage device, > 2 GB primary memory > 2 GB HDD storage device Windows 8.1, > 2 GB primary memory > 2 GB HDD storage device Windows 10, > 2 GB primary memory > 2 GB HDD storage device Windows Server 2008 R2, > 2 GB primary memory > 2 GB HDD storage device Windows Server 2012 R2, > 2 GB primary memory > 2 GB HDD storage device Windows Server 2016, > 2 GB primary memory Microsoft internet explorer 11 External audio and video files .NET Framework 3.5
Software Version	V20.0
Provided Equipment	User's documentation in electronic format
Document type	Technical reference manual Training manual Quick start-up guide
Software Function	Database connection E-signature
Audio video coding standard	WAV AVI MPEG MP4 MP3 MOV

Ordering and shipping details

Category	22574 - MAGELIS BOX PC AND PANEL PC
----------	-------------------------------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	MC2
GTIN	3606489818371
Nbr. of units in pkg.	1
Package weight(Lbs)	2.40 oz (68 g)
Returnability	No

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.04 in (0.1 cm)
Package 1 width	5.51 in (14 cm)
Package 1 Length	5.51 in (14 cm)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[HMIVXLTC](#)