



Main

Accessory / separate part category	Connection accessories
Accessory / Separate Part Type	Connecting cable
Accessory / separate part designation	RS232 connecting cable
Accessory / separate part destination	DTE terminal port
Cable length	8.20 ft (2.5 m)

Complementary

Range Compatibility	Harmony GTO Twido Harmony XBT TSX Micro Modicon Premium automation platform
Electrical connection	1 female connector mini DIN 8 1 female connector SUB-D 9
Kit composition	1 SUB-D 9-way female/25-way male adaptor 1 connecting cable
Communication port protocol	Modbus Uni-Telway Character mode
Physical interface	RS485 RS232
Net Weight	0.37 lb(US) (0.17 kg)

Ordering and shipping details

Category	18225-PLC NTRWK HRDWR & PROWORX SOFTWARE
Discount Schedule	PC41
GTIN	3595862055703
Nbr. of units in pkg.	1
Package weight(Lbs)	8.61 oz (244.0 g)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.98 in (2.5 cm)
Package 1 width	5.91 in (15 cm)
Package 1 Length	5.91 in (15 cm)
Unit Type of Package 2	S04
Number of Units in Package 2	100
Package 2 Weight	55.89 lb(US) (25.35 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	15.75 in (40 cm)
Package 2 Length	23.62 in (60 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[TSXPCX1031](#)