

# ZC2GG1

auxiliary contact block - 1 NO + 1 NC - On delay - for TeSys B



## Main

|                           |                         |
|---------------------------|-------------------------|
| Range of product          | TeSys B                 |
| Range                     | TeSys                   |
| Product or component type | Auxiliary contact block |
| Product compatibility     | CR1B<br>LC1B            |
| Pole contact composition  | 1 NO + 1 NC             |

## Complementary

|                         |  |
|-------------------------|--|
| Mechanical durability   | 1000000 cycles   |
| Connections - terminals | Control circuit screw connection 1 0.01 in <sup>2</sup> (4 mm <sup>2</sup> ) with cable end<br>Control circuit screw connection 1 0.01 in <sup>2</sup> (6 mm <sup>2</sup> ) without cable end<br>Control circuit screw connection 2 0.01 in <sup>2</sup> (4 mm <sup>2</sup> ) with cable end<br>Control circuit screw connection 2 0.01 in <sup>2</sup> (6 mm <sup>2</sup> ) without cable end |

## Ordering and shipping details

|                       |                                |
|-----------------------|--------------------------------|
| Category              | 18073 - SPARE PARTS DISCOUNT I |
| Discount Schedule     | CP2                            |
| GTIN                  | 03389110365481                 |
| Nbr. of units in pkg. | 1                              |
| Package weight(Lbs)   | 1 lb(US) (0.45 kg)             |
| Returnability         | No                             |
| Country of origin     | FR                             |

## Packing Units

|                              |                          |
|------------------------------|--------------------------|
| Unit Type of Package 1       | PCE                      |
| Package 1 Height             | 2.76 in (7 cm)           |
| Package 1 width              | 4.17 in (10.6 cm)        |
| Package 1 Length             | 4.21 in (10.7 cm)        |
| Unit Type of Package 2       | S03                      |
| Number of Units in Package 2 | 25                       |
| Package 2 Weight             | 29.05 lb(US) (13.177 kg) |
| Package 2 Height             | 11.81 in (30 cm)         |
| Package 2 width              | 11.81 in (30 cm)         |
| Package 2 Length             | 15.75 in (40 cm)         |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| California proposition 65  | WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>                   |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                               |
| Mercury free               | Yes  |
| RoHS exemption information | <a href="#">Yes</a>  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>   |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZC2GG1](#)