

Product data sheet

Characteristics

8501KFR13V14

Plug-In Relay - flange mounted - 3 poles - 24VAC coil



Product availability: Stock - Normally stocked in distribution facility



Main

Product range	8501K
Product type	Relay
Relay type	General purpose
Mounting type	Flange
Contact composition	3PDT
[Uc] control circuit voltage	24 V AC
Manual operator	Without

Complementary

Horsepower rating	0.33 hp 120 V 1 hp at 277 V
Maximum switching voltage	300 V at AC 30 V at DC
Contact material	Silver alloy (AgNi)
Operating time	20 ms - pick-up 20 ms - drop-out
Shape of pins	Spade

Environment

Ambient temperature range - operational	-40...131 °F
Product certifications	UL recognized CE CSA RoHS

Ordering and shipping details

Category	21145 - 8501 KF, KL
Discount Schedule	CP2
GTIN	00785901304333
Nbr. of units in pkg.	1
Package weight(Lbs)	0.19
Returnability	Y
Country of origin	CN

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1430 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and

----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[8501KFR13V14](#)