

Product availability: Stock - Normally stocked in distribution facility



Main

Product range	8501R
Product type	Miniature Relay
Relay type	Low voltage

Complementary

Mounting type	Socket
Contact composition	4PDT
[Uc] control circuit voltage	120 V AC
Pilot light	No indicator
Manual operator	Without test button
Horsepower rating	Not rated
Breaking capacity	5 A at 120 V AC - resistive control circuit per UL 508 5 A at 240 V AC - resistive control circuit per UL 508 5 A at 30 V DC - resistive control circuit per UL 508
Maximum switching voltage	30 V at DC 240 V at AC
Contact material	Hermetically sealed silver tin oxide
Operating time	20 ms - pick-up 20 ms - drop-out
Shape of pins	Spade
For use with	8501NR45
Height	29.4 mm
Width	23.1 mm
Depth	1.53 in (38.9 mm)


Environment

Ambient temperature range - operational	-40...131 °F
Product certifications	CE CSA UL listed UL recognized

Ordering and shipping details

Category	21143 - 8501 R
Discount Schedule	CP2
GTIN	00785901031888
Nbr. of units in pkg.	1
Package weight(Lbs)	0.12
Returnability	Y
Country of origin	CN

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0844 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[8501RS34V20](#)