



Main

Bezel material	Black plastic
Control button type	Standard push-button
Device short name	SK
Enclosure type	Corrosion resistance enclosure indoor/outdoor Dust and oil resistant weatherproof enclosure indoor/outdoor
Light source	without
Mounting diameter	1.18 in (30 mm)
Operator additional information	Extended plastic guard

Complementary

Line Rated Current	10 A
Cap/operator or lens colour	red
Contact operation	Standard fingersafe
Contacts type and composition	3 NO + 1 NC
Control type	push-button
Electrical connection	Screw clamp terminal
Light block supply	Without supply Without supply
Marking	unmarked
Mounting support	panel
Operator position information	2 positions
Operator profile	1 projecting push-button
Permissible voltage	600 V
Shape	Round head
Type of operator	Momentary
Utilisation category	AC-15 DC-13

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product Certifications	UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03 CE

Ordering and shipping details

Category	21429-9001 SK,SKY
Discount Schedule	CS1
GTIN	00785901711445
Package weight(Lbs)	8.00 oz (226.796 g)
Returnability	No
Country of origin	MX

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schneider Electric:

9001SKR2RH135