

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch lever
Device short name	9007C
Associated head	9007A 9007B 9007C 9007N 9007T10 9007T5
Associated complete product	9007AW 9007C
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever length: 2 in - offset: - ball bearing roller
Type of roller	1 steel outside roller diameter: 0.69 in - width: 0.25 in
Type of approach	Lateral approach
Positive opening	Without

### Complementary

Switch actuation	By 30° cam
Product weight	0.1 lb(US)

### Environment

Ambient air temperature for operation	-20...185 °F
Ambient air temperature for storage	-20...185 °F
Environmental characteristic	Standard environment

### Ordering and shipping details

Category	21493 - 9007 ARMS FOR AW,C
Discount Schedule	DS1
GTIN	00785901739319
Nbr. of units in pkg.	1
Package weight(Lbs)	0.10000000000000001
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9007CA9](#)