

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

|                             |   |
|-----------------------------|---|
| Range of product            | 9007  |
| Series name                 | Heavy duty  |
| Product or component type   | Limit switch lever  |
| Device short name           | 9007C   |
| Associated head             | 9007A<br>9007B<br>9007C<br>9007N<br>9007T10<br>9007T5           |
| Associated complete product | 9007AW<br>9007C   |
| Movement of operating head  | Rotary  |
| Type of operator            | Cast zinc spring return roller lever length: 3 in - offset: - - |
| Type of roller              | 1 steel inside roller diameter: 0.75 in - width: 0.25 in        |
| Type of approach            | Lateral approach  |
| Positive opening            | Without   |

### Complementary

|                  |            |
|------------------|------------|
| Switch actuation | By 30° cam |
| Product weight   | 0.1 lb(US) |

### Environment

|                                       |                      |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | -20...185 °F         |
| Ambient air temperature for storage   | -20...185 °F         |
| Environmental characteristic          | Standard environment |

### Ordering and shipping details

|                       |                            |
|-----------------------|----------------------------|
| Category              | 21493 - 9007 ARMS FOR AW,C |
| Discount Schedule     | DS1                        |
| GTIN                  | 00785901888703             |
| Nbr. of units in pkg. | 1                          |
| Package weight(Lbs)   | 0.10000000000000001        |
| Returnability         | N                          |
| Country of origin     | MX                         |

### Offer Sustainability

|                                  |   |
|----------------------------------|---|
| RoHS (date code: YYWW)           | Will not be compliant   |
| REACH                            | Reference not containing SVHC above the threshold   |
| Product environmental profile    | Available   |
| Product end of life instructions | Need no specific recycling operations   |
| California proposition 65        | WARNING: This product can expose you to chemicals including:  |
| - - - - - Substance 1            | Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and                               |
| - - - - - Substance 2            | Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. |
| - - - - - More information       | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                             |

## Contractual warranty

---

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9007EA15](#)