

9007MA3

LIMIT SWITCH LEVER ARM AW+C +OPTIONS

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

| | |
|-----------------------------|---|
| Range of product | 9007 |
| Series name | Heavy duty |
| Product or component type | Limit switch lever |
| Device short name | 9007C |
| Associated head | 9007A 9007B 9007C 9007N 9007T10 9007T5 |
| Associated complete product | 9007AW 9007C |
| Movement of operating head | Rotary |
| Type of operator | Cast zinc spring return one way roller lever length: 1.5 in - offset: - - |
| Type of roller | 1 steel outside roller diameter: 1.25 in - width: 0.25 in |
| Type of approach | Lateral approach |
| Positive opening | Without |

Complementary

| | |
|------------------|------------|
| Switch actuation | By 30° cam |
| Product weight | 0.1 lb(US) |

Environment

| | |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | -20...185 °F |
| Ambient air temperature for storage | -20...185 °F |
| Environmental characteristic | Standard environment |

Ordering and shipping details

| | |
|-----------------------|----------------------------|
| Category | 21493 - 9007 ARMS FOR AW,C |
| Discount Schedule | DS1 |
| GTIN | 00785901870432 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.10000000000000001 |
| Returnability | N |
| Country of origin | MX |

Offer Sustainability

| | |
|----------------------------------|---|
| RoHS (date code: YYWW) | Will not be compliant |
| REACH | Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |
| California proposition 65 | WARNING: This product can expose you to chemicals including: |
| - - - - - Substance 1 | Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|------------------------|--|
| ----- Substance 2 | Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. |
| ----- More information | For more information go to www.p65warnings.ca.gov |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9007MA3](#)