



### Overview

Lead time	Usually in Stock
-----------	------------------

### General

Provided Equipment	All required connectors Battery recycling guide Installation guide Reusable packaging
--------------------	--

### Physical

Color	Black
Depth	5.98 in (15.2 cm)
Height	4.02 in (10.2 cm)
Net Weight	14.99 lb(US) (6.8 kg)
Width	5.24 in (13.3 cm)

### Output

Battery Capacity	7.0 Ah
------------------	--------

### Environmental

Ambient air temperature for operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	23...113 °F (-5...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

### Batteries & Runtime

Battery Slots Empty	0
Included Battery Modules	0
Device mounting	Enclosed battery cartridge
Battery Voltage	24 V
Battery Type	Lead-Acid battery
RBC Quantity	1

## Ordering and shipping details

GTIN	00731304260042
Package weight(Lbs)	15.43 lb(US) (7 kg)

## Packing Units

Package 1 Height	5.51 in (14 cm)
Package 1 width	8.27 in (21 cm)
Package 1 Length	6.73 in (17.1 cm)
SCC14	10731304260049

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[APCRBC113](#)