

Main

Asynchronous motor control profile	Variable torque standard
Device short name	ATV61
Range of Product	Altivar 61

Complementary

Line Rated Current	116 A
Cable entry	Type 1 conduit entry outdoor
Communication Port Protocol	Modbus CANopen
Input voltage	400/480 V AC
Keypad Type	LCD keypad
Maximum Horse Power Rating	75 hp
Motor power kW	55 kW
Phase	3 phase input 3 phase output
Output voltage	<= rated supply voltage

Environment

EMC filter	Class A EMC filter integrated
IP Degree of Protection	IP20
NEMA degree of protection	No enclosure rating (open device)
Protective treatment	None

Ordering and shipping details

Category	22138 - ATV61 60 THRU 150 HP DRIVES
Discount Schedule	CP4C
GTIN	00785901854326
Nbr. of units in pkg.	1
Package weight(Lbs)	108.01 lb(US) (48.99 kg)
Returnability	No
Country of origin	CN

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ATV61HD55N4T1](#)