

### Main

Asynchronous motor control profile	Variable torque standard
Device short name	ATV61
Range of Product	Altivar 61

### Complementary

Line Rated Current	4.1 A
Cable entry	Type 1 conduit entry outdoor
Communication Port Protocol	Modbus CANopen
Input voltage	400/480 V AC
Keypad Type	LCD keypad
Maximum Horse Power Rating	2 hp
Motor power kW	1.5 kW
Phase	3 phase input 3 phase output
Output voltage	<= rated supply voltage

### Environment

EMC filter	Class A EMC filter integrated
IP Degree of Protection	IP20
NEMA degree of protection	No enclosure rating (open device)
Protective treatment	None

### Ordering and shipping details

Category	22136 - ATV61 1/2 THRU 5 HP DRIVES
Discount Schedule	CP4C
GTIN	00785901267928
Nbr. of units in pkg.	1
Package weight(Lbs)	12.11 lb(US) (5.49 kg)
Returnability	No
Country of origin	CN

### Contractual warranty

Warranty	18 months
----------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ATV61HU15N4T1](#)